




DO NOT SCALE		METRIC		THIRD ANGLE PROJECTION	
DIMENSIONS IN mm					
LTR	DESCRIPTION	DWN	APPD	DATE	
K1	ECO-09-025714	KK	AEG	17DEC09	

NOTES :

- FOR USE ON MINI HD APPLICATOR (LEFT - RIGHT FEED).
- TINPLATING THICKNESS .000080 MIN _ .000400 MAX. (INCH).
- MATERIAL PH.BRONZE ACC ASTM B103 ALLOY 511.
-  REAR ROLLING MUST TOUCH TAB.


 **5** OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



WIRE	CRIMP HEIGHT	CRIMP WIDTH
0.5mm?	1.43mm	.080 'F'
0.75mm?	1.52mm	.080 'F'
1.0mm?	1.61mm	.080 'F'

 OBSOLETE	100015-4	PRE-TINPLATED	PH.BRONZE	216329-4
	100015-3	SILVERPLATED	PH.BRONZE	216329-3
	100015-2	TINPLATED	PH.BRONZE	216329-2
	100015-1	UNPLATED	PH.BRONZE	216329-1
	LOOSE PIECE NR.	FINISH	MATERIAL	PARTNUMBER
CUSTOMER DRAWING		 TYCO ELECTRONICS AMP ESPAÑOLA S.A. BARCELONA ESPAÑA		
FOR REFERENCE ONLY WILL NOT BE UPDATED		THIS DRAWING IS UNPUBLISHED CUSTOMER DRAWING -		
DR. R.v.Lokven DATE 24.04.89		WIRE RANGE 0.5-1.0mm?		REV.DATE D M Y
CHK. R.v.Lokven DATE 24.04.89		INSUL.RANGE 1.4-2.3 DIA		17 12 09
APP. L.v.Soest DATE 26-11-89		SIZE A2	SHEET 1 OF 1	REV.LTR. K1

DIRECTION OFF TOP OF REEL



107 - 3 FIG 6.