




ITEM #	PART #	QTY	DESCRIPTION
1	AJ-156-11	1	HOUSING, JACK CABLE
2	AJ-156-30	1	INSERT, 6-COND
3	AP-105-5	1	STRAIN RELIEF
4	AP-116-3	1	WASHER, RUBBER
5	AP-136-8	1	NUT ADAPTER WITH GASKET
6	AP-136-6	1	CLAMP, OUTER SHELL
7	AP-136-5	1	CLAMP, SHIELD INNER
8	SEE TABLE #1	1	BUSHING
9	SEE TABLE #1	1	WASHER
10	SEE TABLE #1	1	SPRING
11	AP-116-6	1	STUD

B AJ-156S

TABLE #1				
PART #	CABLE Ø	BUSHING	WASHER	SPRING
AJ-156S/12-1	Ø .165 ± .010	AP-116-17	AP-116-2	AP-116-4
AJ-156S/12-2	Ø .228 ± .010	AP-116-18	AP-116-2	AP-116-4
AJ-156S/12-3	Ø .250 ± .010	AP-116-8	AP-116-2	AP-116-4
AJ-156S/12-4	Ø .290 ± .010	AP-116-19	AP-116-2	AP-116-4
AJ-156S/12-5	Ø .320 ± .010	AP-116-20	AP-116-22	AP-116-21

NOTES:
1) MARK PART NUMBER & MANUFACTURER'S NAME, LOCATED APPROX AS SHOWN



SECTION Z-Z

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF NEXUS, INCORPORATED AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR ANY PURPOSE WITHOUT THE WRITTEN CONSENT OF NEXUS.

B	ADD: AJ-156S; BILL OF MATERIAL	213	10/8 2014	HR
A	NEW RELEASE	135	7/26 2012	HR
LET.	REVISION	CN #	DATE	CHK.

DWN.BY HR	DATE 7/26/12	MATERIAL			
CHECKED BY	DATE	FINISH			
APPR.BY	DATE	WEIGHT —	SCALE = 2.00 :1		NEXUS STAMFORD,CONN
UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES &/OR [mm] TOLERANCES: DECIMAL: .XX[x.x] .XXX[x.xx] ± .01[0.3] ± .003[0.08] FRACTION: X/X ± 1/64 ANGLES: .X ± .5°		TITLE JACK 6-PIN AUDIO CRIMP SLEEVE, SHIELDED			
		DO NOT SCALE DWG.	SHEET 1 OF 1		
		SIZE B	DWG. NO. AJ-156S		