


ODU MINI- SNAP®



Item number: G50L0C-P04NFG0-0000




ODU MINI-SNAP® devices Part
4-pole
protection class IP 50, the front and rear mounting - use Part
twist
chrome Matt: Housing

[Remember the product](#)

[Download PDF](#)

(Example: image representation of the design)



Number of poles: 4 poles



contact insert
4-pin
female
crimp clip contact

Coding 0 °



Insulation material:	PEEK		
Contact diameter:	0.7		
Cable diameter:	from 1.5 mm to 1.5 mm		
Max. Connection cross section:	AWG 22 / 0.38 mm ²		
Connection	diameter	:	0.85 mm

Technical specifications			
Continuity resistance	:	<7 µΩ	
Insulation resistance:	10 ^ 16 Ω		
Air and creepage distance:	0.6 mm	according to IEC 60664-1: 2007 (VDE 0110-1: 2008)	
Current load Single contact:	7 A		
Current load compl. Application:	7 A	VDE 0298-4: 2013	
Test	voltage:	0.9 kV	SAE AS 13441: 2004 method 3001.1
Rated voltage:	0.3 kV	SAE AS 13441: 2004 method 3001.1	

All dimensions in mm. All illustrations are illustrations. Subject to change.

General information about ODU MINI-SNAP Application
temperature: -40 ° C to + 120 ° C

ODU GmbH & Co. KG
Pregelstraße 11
84453 Mühldorf / Inn
Tel: +49 8631 6156-0
Fax: +49 8631 6156-49
E-Mail: central@odu.de

Print date 15.09.2017