







THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A		2017/03/29	Kris	Initial Release
B	CI90405	2019/03/14	Ruru	Modify Note
C	CI90541	2019/04/16	JC Chen	Modified parts

ALTW
CONFIDENTIAL
2019-04-16
R&D DEPT.



Recommended
Panel Cut-out
Front View

- Note:
- * Important Dimension to check
 - * Waterproof Rate: IP67, Mated
 - * Insert Housing: Thermoplastic, Black
 - * Pin: Copper Alloy, Gold Plated
 - * Metal Shell & Jack & Nut: Metal, Nickel Plated
 - * O-Ring: Silicone Gray-Black.
 - * Spring Washer: Stainless steel.
 - * Use without waterproof cap or Dust cap for panel thickness Max:4.2mm
 - * Use with waterproof cap or Dust cap for panel thickness Max:3.0mm
 - * Screw Torque :9~12kgf-cm
 - * Gasket and Nut are packed separately in PE bags.

UNIT:mm		TITLE		Amphenol LTW		ITEM NO	DRAWN BY	DATE
TOLERANCE		RJ45 Cat.6A Receptacle		安費諾亮泰企業股份有限公司		RCM-6APFFH-TCM7001	JC Chen	2019-04-16
.X	±0.25	SCALE	3:2	SIZE	A4	DWG NO	CHECKED BY	DATE
.XX	±0.1	REV.	C	WC-REV.	A.17	RCM-6APFFH-TCM7001	Li Feng	2019-04-16
.XXX	±0.05	SHEET 1 OF 1		QC:Inspection item		CUSTOMER	APPROVED BY	DATE
ANGLES	±1°					ALTW	Jerry	2019-04-16