

THIS DRAWING IS A CONTROLLED DOCUMENT FOR SOURIAU USA, INC.
IT IS SUBJECT TO CHANGE WITHOUT NOTIFICATION.
CONTACT THE DOCUMENT CONTROL CENTER FOR THE LATEST REVISION.

THE INFORMATION CONTAINED IN THIS DRAWING IS CONFIDENTIAL AND MAY NOT BE
DISCLOSED WITHOUT WRITTEN CONSENT FROM SOURIAU USA, INC.


DWG. NO.
JBX0INSFQC

FEMALE INSULATOR, 90° PCB CONTACT

CONTACT LAYOUT	02	03	04	05
FRONT SIDE VIEW				
REAR SIDE VIEW				
CONTACT				
ISO VIEW				
CONTACT	ØC	0.9	0.9	0.7
	ØF	0.58	0.58	0.58
	MAX. AWG	-	-	-
	MAX. CURRENT RATING (A)	10	10	7
	CONTACT RESISTANCE (mΩ)	3.5	3.5	5
INSULATOR	NUMBER OF CAVITY	2	3	5
	MAX. CURRENT RATING	10	8	6.5
	TEST VOLTAGE (Vrms)	1400	1300	800
	WORKING VOLTAGE (Vdc/Vrms)	660/460	600/420	400/260

ORIGIN	COUNTRY	JURISDICTION	CLASSIFICATION
X	FR	Not listed	N/A
	US	EAR	ECCN =EAR99
These commodities, technology or software are exported from the United States in accordance with the Export Administration Regulations. Diversion contrary to U.S. law is prohibited			

LINEAR MEASURE:	
THIRD ANGLE PROJECTION	
TOLERANCES UNLESS OTHERWISE SPECIFIED	
No. OF PLACES	mm [INCH]
ONE PLACE	±3 [±.1]
TWO PLACES	±0.5 [±.02]
THREE PLACES	±0.25 [±.010]
ANGLES±1°	



CONTACT TYPE : F (FEMALE)
CONTACT TERMINATION : Q (90° PCB)
MATERIAL :
CONTACT: CUPRO-NICKEL
CLIP: COPPER ALLOY
INSULATOR: PEEK
FINISH:
CONTACTS : GOLD

CATALOG NUMBER DESCRIPTION

JBXXX 0 XYYF Q XXXX

BASIC SERIES
SHELL TYPE
SHELL SIZE
KEYING
CONTACT LAYOUT
OPTION
INSERT MATERIAL
COLLET OPTION
SURFACE PLATING
CONTACT TERMINATION
CONTACT TYPE

B	REVISED PER ECN 12286	RSK 06-10-15	EV 06-10-15
A	RELEASED PER ECN 12264	TJS 03-10-15	EV 03-10-15
REV	DESCRIPTION	BY DATE	CHKD DATE

DRAWING TITLE
JBX, SIZE 0, FEMALE INSULATOR, 90° PCB CONTACT
CAT NO.


JBX0INSFQ		APPROVAL	
CAGE NO: 09922	SIZE: B	DRAWN: TJS	02-04-15
CUSTOMER		CHKD : EV	02-04-15
		DSGN : EV	02-04-15
INTERPRET THIS DRAWING IN ACCORDANCE WITH ASME Y14.5M - 1994.		MFG : DH	02-04-15
		QC : BB	02-04-15
SOURIAU		DRAWING SCALE: NA	
		DRAWING NO. REV	
WWW.SOURIAU.COM		JBX0INSFQC B	
		1 OF 2	

THIS DRAWING IS A CONTROLLED DOCUMENT FOR SOURIAU USA, INC.
IT IS SUBJECT TO CHANGE WITHOUT NOTIFICATION.
CONTACT THE DOCUMENT CONTROL CENTER FOR THE LATEST REVISION.

THE INFORMATION CONTAINED IN THIS DRAWING IS CONFIDENTIAL AND MAY NOT BE
DISCLOSED WITHOUT WRITTEN CONSENT FROM SOURIAU USA, INC.

DWG. NO.
JBX0INSFQC

FEMALE INSULATOR, 90° PCB CONTACT



SAMPLE ASSEMBLY FOR INFORMATION

LAYOUT	02	03	04	05
A	22.7	22.7	22.7	25.2
B	31.9	31.4	31.7	31.9

LAYOUT	02	03	04	05
PCB LAYOUT VIEW F DIRECTION				
1. ALL DIMENSIONS ARE ± 0.05 2. RECOMMENDED FINISHED PCB HOLE SIZE $\varnothing 0.83$ MIN.				

ORIGIN	COUNTRY	JURISDICTION	CLASSIFICATION
X	FR	Not listed	N/A
	US	EAR	ECCN =EAR99
These commodities, technology or software are exported from the United States in accordance with the Export Administration Regulations. Diversion contrary to U.S. law is prohibited			

LINEAR MEASURE: mm (INCH)	
THIRD ANGLE PROJECTION	
TOLERANCES UNLESS OTHERWISE SPECIFIED	
No. OF PLACES	mm [INCH]
ONE PLACE	± 3 [$\pm .1$]
TWO PLACES	± 0.5 [$\pm .02$]
THREE PLACES	± 0.25 [$\pm .010$]
ANGLES $\pm 1^\circ$	

DRAWING TITLE						
JBX, SIZE O, FEMALE INSULATOR, 90° PCB CONTACT						
CAT NO.						
JBXOINSFQ						
CAGE NO: 09922		SIZE: B		APPROVAL		
CUSTOMER		SOURIAU				
					DRAWN: TJS	02-04-15
					CHKD : EV	02-04-15
					DSGN : EV	02-04-15
					MFG : DH	02-04-15
INTERPRET THIS DRAWING IN ACCORDANCE WITH ASME Y14.5M - 1994.		QC : BB			02-14-15	
		DRAWING SCALE: NA				
		DRAWING NO.		REV		
		JBXOINSFQC		B		
		2 OF 2				