

IE-PS-M12X-S-FH**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems. The IDC is simple and quick to assemble since this technology allows the conductor to be inserted directly into the terminal point, without crimping or having to strip the insulation. It also has excellent functional security.

General ordering data

Version	Sockets prefabricated to customer spec., M12, IDC, IP67 plugged
Order No.	1516330000
Type	IE-PS-M12X-S-FH
GTIN (EAN)	4050118323788
Qty.	1 pc(s).

IE-PS-M12X-S-FH

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	23 g
------------	------

Temperatures

Operating temperature	-40 °C...85 °C
-----------------------	----------------

Environmental Product Compliance

REACH SVHC	SCIP	67cf1078-beca-4687-860b-dc475a6ec24a
Lead 7439-92-1		

Technical data customisable plug-in connectors

Coding	X	Contact surface	Gold-plated
Housing main material	Zinc diecast	Insulation strength	100 MΩ
Number of poles	8	Plugging cycles	≥ 100
Protection degree	IP67 plugged	Rated voltage	48 V

General Info

Connection 1	M12	Connection 2	IDC
Housing main material	Zinc diecast	Insulation cross-section, max.	1.6
Connection thread	M12	Contact material	Brass
Contact surface	Gold-plated	Connection diameter, solid	0.4...0.64
Wire connection diameter, solid, min.	0.4	Conductor connection cross-section, solid (AWG)	AWG 24...AWG 22
Wire connection diameter, solid, max.	0.64	Connection diameter, flexible	0.48...0.76 mm
Wire cross-section, solid, min. (AWG)	AWG 24	Conductor connection cross-section, flexible (AWG)	AWG 26...AWG 22
Wire cross-section, solid, max. (AWG)	AWG 22	Wire connection diameter, flexible, min.	0.48 mm
Wire connection diameter, flexible, max.	0.76 mm	Wire cross-section, finely stranded, min. (AWG)	AWG 26
Wire cross-section, finely stranded, max. (AWG)	AWG 22	Sheath diameter, min.	5 mm
Sheath diameter, max.	9.7 mm	Contact holder materials	PA
Shielding	360° all-round enclosure	Protection degree	IP67 plugged
Plugging cycles	≥ 100		

Electrical properties

Current-carrying capacity at 50 °C	0.5 A @ 40 °C	Insulation strength	100 MΩ
PoE / PoE+	conforming to IEEE 802.3at	Rated voltage	48 V

General standards

Certificate no. (cULus)	E316369	Connector standard	IEC 61076-2-109
-------------------------	---------	--------------------	-----------------

Standards

Connector standard	IEC 61076-2-109	Fire safety for railway vehicles	DIN EN 45545-2
--------------------	-----------------	----------------------------------	----------------

IE-PS-M12X-S-FH

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Classifications

ETIM 6.0	EC002635	ETIM 7.0	EC002635
ETIM 8.0	EC002635	ECLASS 9.0	27-44-01-02
ECLASS 9.1	27-44-01-03	ECLASS 10.0	27-44-01-02
ECLASS 11.0	27-44-01-02	ECLASS 12.0	27-44-01-16

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E316369

Downloads

Approval/Certificate/Document of Conformity	DUXR.E316369 CC Link IE Field M12-X PROFINET Manufacturer's Declaration
Engineering Data	CAD data – STEP
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN Manual
Catalogues	Catalogues in PDF-format
Brochures	MB FREECONTACT EN FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN

IE-PS-M12X-S-FH

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensioned drawing

