



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER ECO-15-006978	06JUN2015	NK	MM



- 1 WIRE RANGE IS FOR 2 AWG. STANDARD WIRE CROSS SECTIONAL AREA RANGE: 52,600-83,700 CMA, STRANDED WIRE.
- 2 TERMINAL BODY MATERIAL THK IS 1.778±0.076[.070±.003].
- 3 RECOMMENDED OPERATING TEMP -55°C [131°F] TO +200°C [392°F] FOR HEAT SHRINK TUBING
- 4 HEAT SHRINK TUBING SHELF LIFE OF 18 MONTHS FROM DATE CODE ON LABEL
- 5 TERMINAL BODY PRODUCT SPECIFICATION 108-32046. APPLICATION SPECIFICATION 114-2162.

1	1-1196717-9	HIGH AND LOW TEMPERATURE CROSS LINKED FLUOROPOLYMER HEAT SHRINK TUBING 15.88[.625]MIN IDX38.10±2.03[1.50±.08] RT555-5/8-O-SP
1	320741-1	TERMINAL BODY: COPPER PER ASTM B152 ANNEALED FINISH: NICKEL PLATE 0.00762 [.000300] MIN EXT THK PER SAE AMS QQ-N-290
-1	PART NO	DESCRIPTION

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 08DEC09	 TE Connectivity				
DIMENSIONS: mm [INCHES]		CHK TOM MICHIELUTTI 08DEC09					
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127 [.005] 4 PLC ± - ANGLES ± 1°	APVD TOM MICHIELUTTI 08DEC09	NAME - HEAT RESISTANT TERMINAL KIT, WIRE SIZE: 2 AWG				
		PRODUCT SPEC - 					
		APPLICATION SPEC - 	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO -	
		WEIGHT -	A3	00779	C-696645		
MATERIAL SEE TABLE	FINISH SEE TABLE	CUSTOMER DRAWING			SCALE 5:1	SHEET 1 of 1	REV B