





LOC	DIST	REVISIONS						
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD	
		C		REVISED PER ECO-10-018054	04NOV2010	CJV	EJB	
		D		REVISED PER ECO-12-003481	15MAR2012	KS	AC	
		E		REVISED PER ECO-12-005533	31MAR2012	JY	AC	
		F		REVISED PER ECO-14-017735	30EC2014	RG	MC	



DETAIL S
SCALE 20:1

- 1 CAGE ASSEMBLY MATERIAL: NICKEL SILVER, 0.25 THICK
HEAT SINK MATERIAL: ALUMINUM
HEAT SINK CLIP MATERIAL: STAINLESS STEEL
EMI SPRING MATERIAL: COPPER ALLOY
FRONT FLANGE MATERIAL: ZINC ALLOY
LIGHT PIPE MATERIAL: CLEAR POLYCARBONATE
- 2 PITCH BETWEEN PORTS OF ONE 1X4 CAGE ASSEMBLY.
- 3 SPACING BETWEEN CAGES ON THE SAME PC BOARD, TO BE SPECIFIED BY CUSTOMER, MUST COMPLY WITH MINIMUM DIMENSIONS SHOWN.
- 4 REFERENCE APPLICATION SPEC 114-13218 FOR RECOMMENDED DRILL HOLE DIAMETER AND PLATING THICKNESS.
- 5 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- 6 DIMENSION F IS THE NOMINAL THICKNESS OF CUSTOMER SUPPLIED PC BOARD, SINGLE SIDED PC BOARD MINIMUM THICKNESS = 1.45mm
DOUBLE SIDED PC BOARD MINIMUM THICKNESS = 2.2mm PER QSFP.
- 7 HEAT SINKS, LIGHT PIPES, AND HEAT SINK CLIPS SHIPPED ASSEMBLED TO CAGE ASSEMBLY. CAGE ASSEMBLY MAY BE PRESSED INTO THE PCB AS SHIPPED.
- 8 DATUM -A- IS TOP SURFACE OF PC BOARD.
- 9 DIMENSION APPLIES WITH MODULE INSERTED IN CAGE.
- 10 UNPLATED THRU HOLE.
11. MATES WITH QSFP MSA COMPATIBLE TRANSCEIVER.
- 12 SURFACE TRACES PERMITTED WITHIN THIS AREA EXCEPT WHERE CAGE STANDOFFS, SHOWN IN DETAIL S, CONTACT PC BOARD.
- 13 BASELINE FOR THESE DIMENSIONS IS THE CENTER OF COMPLIANT PIN HOLE.
- 14 2D BARCODE AND DATE CODE (YYWWDD) MARKED ON SIDE OF CAGE ASSEMBLY.


- 15 REFERENCE APP SPEC 114-13218 FOR GASKET THICKNESS CALCULATION.
- 16 EMI SPRING FINISH: 2µm MINIMUM TIN
FRONT FLANGE FINISH: 3µm MINIMUM TIN OVER 1.27µm MINIMUM NICKEL OVER 5.08µm MINIMUM COPPER.
HEAT SINK FINISH: NICKEL
- 17 HEAT SINKS AND CLIPS SHIPPED ASSEMBLED TO CAGE ASSEMBLY. CAGE ASSEMBLY MAY BE PRESSED INTO THE PCB AS SHIPPED. LIGHT PIPES, SHIPPED UNATTACHED, MUST BE ASSEMBLED BY CUSTOMER AFTER THE CASE IS SEATED IN THE PCB.



1	1.3-1.4	5.7	2.15	16.0	SAN	2057183-5
1	1.3-1.4	5.7	2.15	13.7	PCI	2057183-4
1	0.8-1.1	2.8	1.70	23.0	NETWORKING	2057183-3
1	0.8-1.1	2.8	1.70	16.0	SAN	2057183-2
1	0.8-1.1	2.8	1.70	13.7	PCI	2057183-1
	E	D	C	B	HEAT SINK PROFILE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. VALENTINE 01MAY2008	TE Connectivity			
		CHK E. BRIGHT 01MAY2008				
		APVD F. BRIGHT 01MAY2008	NAME 1X4 CAGE ASSEMBLY, BEHIND BEZEL, W/ LIGHT PIPES AND HEAT SINKS, QSFP			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		SIZE CAGE CODE DRAWING NO		
mm		0 PLC ±.1		RESTRICTED TO		
		1 PLC ±0.1				
		3 PLC ±.1				
		4 PLC ±.1				
		ANGLES ±.1				
MATERIAL		FINISH				
1		16				
		CUSTOMER DRAWING				
		SCALE 4:1		SHEET 1 OF 5		
				REV F		

LOC		DIST		REVISIONS					
GP		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
				-	-	SEE SHEET 1	-	-	-



DOUBLE LIGHT PIPES
QUANTITY: 4


HEAT SINK CLIPS
QUANTITY: 4

72 PIN HEAT SINKS
QUANTITY: 4


1X4 BEHIND BEZEL QSFP
CAGE ASSEMBLY
QUANTITY: 1

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN	C. VALENTINE	01MAY2008	 TE Connectivity			
				CHK	E. BRIGHT	01MAY2008				
				APVD	F. BRIGHT	01MAY2008	NAME			
DIMENSIONS: mm 				TOLERANCES UNLESS OTHERWISE SPECIFIED:			1X4 CAGE ASSEMBLY, BEHIND BEZEL, W/ LIGHT PIPES AND HEAT SINKS, QSFP			
				PRODUCT SPEC			SIZE			
				108-2286						
				APPLICATION SPEC			CAGE CODE			
				114-13218						
				WEIGHT			DRAWING NO			
MATERIAL				CUSTOMER DRAWING			RESTRICTED TO			
							A100779C=2057183			
							SCALE			
							4:1			
							SHEET			
							2			
							OF			
							5			
							REV			
							F			



LOC		DIST		REVISIONS			
GP		00		P	LTR	DESCRIPTION	DATE
						SEE SHEET 1	



ONE SIDED CONFIGURATION
SCALE 5:2



BELLY TO BELLY CONFIGURATION
SIMILAR TO ONE SIDED
EXCEPT WHERE NOTED
SCALE 5:2



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. VALENTINE CHK E. BRIGHT APVD F. BRIGHT	01MAY2008 01MAY2008 01MAY2008	TE Connectivity	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
mm		0 PLC ± 0.1 1 PLC ± 0.1 2 PLC ± 0.1 3 PLC ± 0.1 4 PLC ± 0.1 ANGLES ± 0.1 FINISH		1X4 CAGE ASSEMBLY, BEHIND BEZEL, W/ LIGHT PIPES AND HEAT SINKS, QSFP	
MATERIAL		CUSTOMER DRAWING		SIZE CAGE CODE DRAWING NO	
				A100779C=2057183	
				RESTRICTED TO	
				SCALE 4:1 SHEET 3 OF 5 REV F	



LOC		DIST		REVISONS			
GP				P	LTR	DESCRIPTION	DATE
				-		SEE SHEET 1	

D


C

B

A



DETAIL M
SCALE 10:1




DETAIL J
3 PLACES
SCALE 8:1

RECOMMENDED PC BOARD LAYOUT
SINGLE SIDE MOUNT CONFIGURATION
SCALE 4:1

THIS PRODUCT HAS NOT COMPLETED VALIDATION/QUALIFICATION TESTING

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. VALENTINE	01MAY2008	 TE Connectivity	
DIMENSIONS:		CHK E. BRIGHT	01MAY2008		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD F. BRIGHT	01MAY2008	NAME 1X4 CAGE ASSEMBLY, BEHIND BEZEL, W/ LIGHT PIPES AND HEAT SINKS, QSFP	
	0 PLC ±	PRODUCT SPEC		SIZE A1	CAGE CODE 00779
	1 PLC ±0.1	108-2286			
	2 PLC ±0.1	APPLICATION SPEC			
	3 PLC ±	114-13218			
MATERIAL :	FINISH :	WEIGHT -	DRAWING NO 2057183		RESTRICTED TO -
CUSTOMER DRAWING			SCALE 4:1	SHEET 4 OF 5	REV F

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
GP	00	-	-	SEE SHEET 1	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. VALENTINE CHK E. BRIGHT APVD F. BRIGHT	01MAY2008 01MAY2008 01MAY2008	TE Connectivity	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
mm		0 PLC $\pm$ 1 PLC ± 0.1 2 PLC ± 0.1 3 PLC $\pm$ 4 PLC $\pm$ ANGLES $\pm$ FINISH		1X4 CAGE ASSEMBLY, BEHIND BEZEL, W/ LIGHT PIPES AND HEAT SINKS, QSFP	
MATERIAL		WEIGHT		SIZE	RESTRICTED TO
-		-		A100779C=2057183	-
CUSTOMER DRAWING		SCALE 4:1		SHEET 5 OF 5	REV F