






REV.	ECN. NO.	APPD.



SCHEMATIC



RECOMMENDED PCB LAYOUT

Specification

Operating Life	200,000 cycles
Operating Force	F
Maximum Voltage	12 VDC
Max Current	50 mA
Dielectric Strength	250 V AC(1mm)
Contact Resistance	<100 mΩ
Insulation Resistance	>100M Ω
Bounce Time	<5 ms
Storage Temperature	-30° C to 85° C

F (force)		H (height)		THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF YIYUAN TECHNOLOGY CO.,LTD. AND SHOULD NOT BE REPRODUCED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF YIYUAN TECHNOLOGY CO.,LTD.		FINISH		PART NO.		深圳市怡远科技有限公司 SHENZHEN YIYUAN TECHNOLOGY CO., LTD	
X.	± 0.50	X. °	± 2°			UNITS		mm	YIYUAN		
.X	± 0.30	.X°	± 1°								
.XX	± 0.10	.XX°	± 0.5°			MAT'L					
.XXX	± 0.05										
NO.		Force		12		12mm		DR: BILLY WANG 2020/08/21		DWG NO.: YTS 125S X X	
M	180gf ± 50	12P		12mm with pegs		CHKD: ROC					
K	250gf ± 50										
										TITLE: TACTILE SWITCH 12 TH	