

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- . - .

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	M3	REVISED PER ECO-11-004820	11MAR11	RK	HMR
	M4	REVISED PER ECO-17-014338	20APR2018	RS	DR

AMP
WIRE RANGE



Listed
FILE E13288





LR7189
Certified

16-14 AWG
SOLID OR STRANDED

16-14 AWG
SOLID OR STRANDED

16-14 AWG
SOLID OR STRANDED



- 1 WIRE INSUL DIA,
2.921-4.318[.115-.170]
- 2 NOTE DELETED

I	50	LOOSE PIECE, BAG	8-34071-5
I	5	LOOSE PIECE, BLS	8-34071-4
I	100	LOOSE PIECE, BOX	8-34071-1
2	2500	ON TAPE, REEL	2-34071-3
2	1000	LOOSE PIECE	2-34071-2
I	2500	ON TAPE, REEL	2-34071-1
I	1000	LOOSE PIECE	34071
STYLE	QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

MAX RECOMMENDED OPERATING
TEMPERATURE:

105°C [221° F]

VOLTAGE RATING:
600V MAX
(1000V FIXTURE OR SIGN)

CIRCULAR MIL AREA:
1.04-2.62mm² [2,050-5,180]
SOLID OR STRANDED

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111


FOR ORDER ENTRY

1-800-526-5142

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]



MATERIAL
BODY, CU ASTM B 152
INSULATION: PVC

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± 0.127[.005]
4 PLC ± -
ANGLES ± -

FINISH
BODY:TIN PLATE ASTM B545
INSULATION: COLOR-BLUE

DWN 19JUL95

M ELLIS

CHK 19JUL95

C PRESNELL

APVD 19JUL95

S BORTNER

PRODUCT SPEC

UL486A-B

APPLICATION SPEC

114-2161

WEIGHT

CUSTOMER DRAWING



TE Connectivity Ltd.

SPLICE, BUTT, PLASTI-GRIP
WIRE SIZE 16-14 AWG

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C=34071	-

SCALE 4:1

SHEET 1 OF 1

REV M4