

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION






© COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
AF	50	P	LTR	DESCRIPTION	DATE	DWN	APVD
			E	REV PER 0G3A-0696-03	04NOV03	JR	GP
			E1	REVISED PER ECO-10-000443	18JAN10	KK	HMR
			E2	REVISED PER ECR-12-021718	18DEC12	F.M	YHM

- 1 INSULATED HEATER WIRE: #18-16 AWG.
HEATER WIRE CORE DIA: 1.02 MAX
- 2 REF CRIMP INFO: WIRE BBL .090, F TYPE
INSULATION BBL .120, F TYPE
- 3 TRAVERSE WINDING ON METAL REEL.
- 4 IN-LINE WINDING ON A CARDBOARD REEL
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



R 0.58

R 1.02

5 OBSOLETE	7,500	4.44	3.8	3	#14-12 AWG	PRE-TIN	1438246-6
	5,000	4.44	3.8	4	#14-12 AWG	-	1438246-5
	5,000	3.18	3.3	4	#18-16 AWG	-	1438246-4
	7,500	4.44	3.8	3	#14-12 AWG	-	1438246-3
	5,000	3.18	3.3	4	#18-16 AWG	PRE-TIN	1438246-2
	12,500	3.18	3.3	3	#18-16 AWG	-	1438246-1
PCS/REEL		"L"	"A"	NOTES	STD. WIRE SIZE	FINISH	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN B.P	21MAY2002	 Tyco Electronics Corporation Harrisburg, PA 17105			
				CHK F.M	21MAY02				
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD YH.M	21MAY02	NAME			
		0 PLC ± -		PRODUCT SPEC		SPLICE, BUTT, HEATER WIRE -			
		1 PLC ± -		—					
		2 PLC ± 0.35		APPLICATION SPEC					
		3 PLC ± -		—					
		4 PLC ± -		—					
ANGLES ± -						SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
MATERIAL 081M BRASS		FINISH SEE TABLE		WEIGHT —		A2 00779		C=1438246	
CUSTOMER DRAWING						SCALE 10:1		SHEET 1 of 1	
								REV E2	