




SPECIFICATIONS

ELECTRICAL CHARACTERISTICS:

Contact Current Rating:3 Amperes.

Dielectric Withstanding Voltage: AC 1000/60sec.r.m.s.

Insulation Resistance:5000 Megohms Minimum.at DC 500V.

Contact Resistance:25 Milliohms Maximum.

Operating Temperature:-55°C to+105°C.

MECHANICAL CHARACTERISTICS:

Contact Insertion Force:341 g.Maximum.

Contact Separation Force:21 g.Minimum.

MATERIALS:

Contacts:Brass.

Insulator: PBT Or High Temperature Plastic

UL 94V-0 Rated.

Shell:Cold Roller Steel.

Screw:Steel.

FINISHES:

Contact:Gold Flash Or Full Gold.

Shell:Tin Or Nickel Plated.

Screw:Nickel Plated.



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2' X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: HDR15F对HDR15F 铆锁8.89 间距15.88
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW177-VGA30B-158B
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO. DRAW NO: HYC-2209191738
			SHEET NO. 1 OF 1