

强能电气有限公司

304 不锈钢电缆固定头



强能型号 标准螺牙	线缆范围 mm	螺纹外径 mm	螺纹长度 mm	扳手尺寸 螺母/螺帽	304 不锈钢 电缆固定头	备注
PG7S	3-6.5	12.5	7	14/14	8.14	
PG7	4-8	12.5	8	17/17	8.14	
PG9	4-8	15.2	8	18/18	8.8	
PG11	5-10	18.6	9	22/22	8.8	
PG13.5	6-12	20.4	9.5	24/24	9.35	
PG16	9-14	22.5	9.5	25/25	10.45	
PG21	13-18	28.3	12	30/30	14.08	
PG29	18-25	37	12.5	40/40	21.45	
PG36	24-30	47	15	50/50	31.02	
PG42	31-41	54	15	59/59	41.25	
PG48	35-45	59.3	17	67/65	74.25	
M8×1.25	2-3.8	8	5.5	13/13	8.14	
M10×1.5	3-6.5	10	6.5	14/14	8.14	
M12S	3-6.5	12	7	14/14	8.14	
M12	4-8	12	8	17/17	8.14	
M16S	4-8	16	9	18/18	8.8	
M16	5-10	16	9	22/22	8.8	
M20S	6-12	20	9.5	24/24	9.35	
M20	9-14	20	9.5	25/25	10.45	
M25	13-18	25	12	30/30	14.08	
M32	18-25	32	12.5	40/40	21.45	
M40	24-30	40	15	50/50	28.75	
M50	31-41	50	15	59/59	40	
M63	35-45	63	17	67/65	65	

M63 大号	44-51	63	17	73/73	74.25	
M75×2	56-66	75	15	85/88	160	

备注：以上不锈钢电缆固定头型号，如需要加厚小孔线缆范围的，或 NPT 牙和 G (PF) 牙的，请另外咨询我们。谢谢！

- 1) 以上价格不含税和运费，开票另加 12%
- 2) 材质：优质 304 不锈钢；三元乙丙耐候橡胶
尼龙 PA66（UL 认证材料）；
- 3) 报价有效期为 2 个月
- 4) 电话：0577-61679080

