








3D View



RECOMMENDED PCB LAYOUT
TOLERANCE: ±0.05MM (FOR REFERENCE ONLY)



METAL MASK T=0.08
TOLERANCE: ±0.05MM (FOR REFERENCE ONLY)



(For Reference Only)
Stated At Compression

NOTES:

1: MATERIAL

1-1: SUS-301 THICKNE=0.08MM

2: SPECIFICATIONS

2-1: RATED CURRENT: 1.0A

2-2: VOLTAGE RATING: 1.5V

2-3: CONTACT RESISTANCE: 80mΩ/MAX

2-4: WELDING THRUST: ≥3KG

2-5: OPERATING TEMPERATURE: -40°C~+85°C

3: DURABILITY: 1500 CYCLES

4: SALT SPRAY TIME: 24H

5: ELECTROPLATE: THE NICKEL-PLATED SUBSTRATE IS 50u" MIN

6: REQUIREMENTS

6-1: TERMINAL TO EAT FULL TIN, NOT PEELING,
WELDING OBVIOUS COLOR AND OTHER ADVERSE

6-2: ROHS, REACH, HF HALOGEN ADVERSE OF DOMESTIC
AND INTERNATIONAL ENVIRONMENTAL REQUIREMENTS



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2' X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 天线弹片 L1. 80*W1. 30*H2. 60	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	HYCW-TXT181326A
APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO:	HYC-2412181633	
		SHEET NO.	1 OF 1	