








PIN No	DESCRIPTION
C1	VCC : SUPPLY VOLTAGE
C2	RST : RESET SIGNAL
C3	CLK : CLOCK SIGNAL
C4	RESERVED
C5	GND
C6	VPP : VARIABLE SUPPLY VOLTAGE
C7	I/O : SERIAL DATA INPUT/OUTPUT
C8	RESERVED

备注:

1. 材质:

1.1 胶芯: LCP S475 UL94V-0;

1.2 端子: C5210, 镍底50U"MIN, 接触区域镀金1U"MIN; 焊脚镀刷金.

1.3 外壳: SUS304-1/2, 整体镀可焊镍50U"MIN. 焊接区域刷金.

2. 主要特性:

2.1 额定电流: 1.0A/PCS MAX

2.2 额定电压: 12V AC;


2.3 接触阻抗: 60mΩ MAX;

2.4 绝缘阻抗: 1000mΩ MIN 100V DC;

2.5 耐压测试: 500V AC 每分钟;


2.6 使用寿命: 5000次;

2.7 工作温度: -30℃~+80℃.



RECOMMENDED PCB LAYOUT


TOLERANCE: ±0.05



MICRO SIM CARD



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: MICRO SIM 8P 1.5H (防锁P)	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW238-SIM08-150B	MOLD NO.
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱国夷	DATE : 2014-02-23	DRAW NO: HYC-SIM191122172	SHEET NO. 1 OF 1