






3D VIEW



WORKING STATE



- 1.MATERIAL SPECIFICATION:
1.1.YCUT-FX-EH T=0.08±0.005MM
- 2.TEST REQUIREMENTS:
2.1.CONTACT RESISTANCE: 80mΩ MAX
2.2.VOLTAGE RATING: 1.5 V/AC/DC/MAX
2.3.RATED CURRENT: 1.0A/MAX
2.4.WELDING THRUST: ≥3.0 Kg
2.5.DURABILITY: 1,500 TIMES
2.6.OPERATING TEMPERATURE: -20 ° ~ 80 ° C
- 3.PLATING REQUIREMENTS:
3.1.THE NICKEL-PLATED SUBSTRATE IS 50U MIN,
3.2.SALT SPRAY TEST TO MEET THE REQUIREMENTS OF 24 HOURS.
3.3.TERMINAL TO EAT FULL TIN, NOT PEELING, WELDING, OBVIOUS COLOR AND OTHER ADVERSE
3.4.ROHS, REACH, HF HALOGEN-FREE AND A SERIES OF DOMESTIC AND INTERNATIONAL ENVIRONMENTAL REQUIREMENTS

RECOMMENDED PCB LAYOUT
TOLERANCE: ±0.05

深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 天线弹片 L2.55*W1.20*H3.90
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW-TXT2551239A
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.
			DRAW NO: HYC-2412201058
			SHEET NO. 1 OF 1