






RECOMMENDED PC BOARD LAYOUT
TOLERANCE:±0.05(TOP VIEW)

NOTES:

1) MATERIAL:

- 1-1 HOUSING:THERMOPLASTIC,UL 94V-0;COLOR:BLACK
- 1-2 SHIELDED:STAINLESS STEEL
- 1-3 CONTACT:COPPER ALLOY
- 1-4 SWITCH PIN:COPPER ALLOY

2) FINISH:

- 2-1 CONTACT: Au PLATING ON CONTACT AREA
(SEE P/N DESCRIPTION)
50u" MIN NICKEL UNDERPLATING OVER ALL
1u"MIN AU PLATING ON SOLD AREA,
- 2-2 SHIELDED:1u" MIN Au PLATING ON SECURED AREA

3) PRODUCT SPECIFICATIONS:

- 3-1 VOLTAGE RATING: 50V
- 3-2 WITHSTANDING VOLTAGE: AC250V R.M.S
- 3-3 CURRENT RATING: 0.5A
- 3-4 INSULATION RESISTANCE: 1000MEG.OHM MIN AT DC 250V
- 3-5 CONTACT RESISTANCE: 100 MILL.OHM MAX
- 3-6 OPERATION TEMPERATURE: -20° TO +85°



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: NANO SIM 1.5H	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW229-SIM06-150B	MOLD NO.
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱国夷	DATE : 2014-02-23	DRAW NO: HYC-SIM18050820	SHEET NO. 1 OF 1