


深圳市顺天五金制品有限公司

产品规格书

客户:	深圳市立创商城		
供应商名称:	深圳市顺天五金制品有限公司		
规格名称:	杯头内六角螺丝, GB70-76, M10*30, 白锌		
客户料号:	C5333904		
样板数量:	6 PCS		
参考标准	外观检查		Ok
	✓ <input type="checkbox"/> 客户标准		OK
	抽样数量: 6		OK


产品信息 PRODUCT INFORMATION



对公差要求高者慎拍以实物为准

公称直 径 d	螺距 P	b	dk	k	s	t	单位:mm							
			mm	min	max	mm	min	max	mm	min	max	mm	min	max
M1.6	0.35	15	3.14	2.86	1.60	1.46	1.5	1.580	1.520	0.7				
M2	0.4	16	3.98	3.62	2.00	1.86	1.5	1.580	1.520	1				
M2.5	0.45	17	4.68	4.32	2.50	2.36	2	2.080	2.020	1.1				
M3	0.5	18	5.68	5.32	3.00	2.86	2.5	2.580	2.520	1.3				
M4	0.7	20	7.22	6.78	4.00	3.82	3	3.080	3.020	2				
M5	0.8	22	8.72	8.28	5.00	4.82	4	4.095	4.020	2.5				
M6	1	24	10.22	9.78	6.00	5.7	5	5.140	5.020	3				
M8	1.25	25	13.27	12.73	8.00	7.64	6	6.140	6.020	4				
M10	1.5	32	16.27	15.73	10.00	9.64	8	8.175	8.025	5				
M12	1.75	36	18.27	17.73	12.00	11.57	10	10.175	10.025	6				
M14	2	40	21.33	20.67	14.00	13.57	12	12.212	12.032	7				
M16	2	44	24.33	23.67	16.00	15.57	14	14.212	14.032	8				
M20	2.5	50	30.33	29.67	20.00	19.4	17	17.05	16.05	10				
M24	3	56	36.39	35.61	24.00	23.19	19	19.275	19.0	不				
M30	3.5	72	45.39	44.61	30.00	29.48	22	22.275	22.0	顶部				
M36	4	84	54.46	53.54	36.00	35.38	27	27.275	27.065	19				
M42	4.5	96	63.46	62.54	42.00	41.38	32	32.33	32.08	24				
M48	5	108	72.46	71.54	48.00	47.38	36	36.33	35.08	28				
M56	5.5	124	84.54	83.46	56.00	55.26	41	41.33	41.08	34				
M64	6	140	96.54	95.46	64.00	63.26	46	46.33	46.08	38				

8.8级镀锌 10 个



M10*30



尺寸与功能检验(抽样按工作指引) (单位:mm)

检验项目	检验标准	样本数 (PCS)	不良数 (PCS)	检验工具	测试数据, 判定结果
柱头长度: K	10.00mm±0.015	6	/	游标卡尺	9.88/9.89/9.89/9.90/9.88
螺纹长度: L	30.00mm	6	/	游标卡尺	29.90/29.89/29.88/29.90/29.90
螺纹直径 d	M10	6	/	游标卡尺	9.92/9.92/9.90/9.90/9.90/9.90
螺头直径 dk	16±0.15mm	6	/	游标卡尺	15.88/15.88/15.93/15.90/15.88
六角对边	8 MM :				
判定结果	✓ <input type="checkbox"/> 合格			客户 确认	
	<input type="checkbox"/> 不合格				
制表	黄文标	审核	王小姐	批准	赖生
日期:	2024-11-27	日期:	2024-11-27	日期:	2024-11-27