


### General information

Part number	S21LFC-P02MPH0-620S	 <small>Illustrations may differ from original product.  Dimensions, unless otherwise specified, in mm.</small>
Termination	solder	
Size	1	
Locking principle	push	
Coding	f_key	
Cable Diameter	cable_mini_62	
Cable outlet	bend_relief	



The pin layout corresponds to the view on the termination area

### Contact insert description

Number of contacts	2
Contact type	pins
Contact diameter	13mm
Insulator material	peek
Wire cross section	20_awg
Termination	solder
Termination diameter	11mm

reverse\_gender\_on\_request

### Technical information

Max. creepage and air clearance distance	10_mm	11_mm
Nominal current single contact	12_a	iec_60512_5_2
Nominal current insert	12_A	vde_0298_4
Test voltage	165_kv_ac	sae_13441
safety_text		

## Mechanical and environmental data

Degree of protection*	ip50
Operating temperature	40_120_c
Mating cycles	5000

mated\_unmated

## Material and surface treatments

Housing	m_chrome
Contact	cu_alloy_gold

safety\_text\_2

ul\_text

illustrative\_text