







3D View





## NOTES

- (1) MATERIAL: C5210 THICKNE=0.08mm
- (2) PRODUCT SPECIFICATIONS:
  - 2-1: RATED CURRENT: 2.0A
  - 2-2: VOLTAGE RATING: 10.0V
  - 2-3: CONTACT RESISTANCE: 50mΩ/MAX
  - 2-4: WELDING THRUST: ≥3KG
  - 2-5: OPERATING TEMPERATURE: -40°C~+85°C
  - 2-6: DURABILITY: 1500 CYCLES
- (3) SALT SPRAY: 24 HOURS
- (4) FINISH: 50u"Min NICKEL UNDERLATING OVER ALL.
- (5) REQUIREMENTS
  - 5-1: TERMINAL TO EAT FULL TIN, NOT PEELING
  - 5-2: WELDING OBVIOUS COLOR AND OTHER ADVERSE
  - 5-3: ROHS, REACH, HF HALOGER ADVERSE OF DOMESTIC AND INTERNATIONAL ENVIRONMENTAL REQUIREMENTS



RECOMMENDED PCB LAYOUT  
TOLERANCE ±0.05 (焊盘推荐图)



深圳市华宇创精密电子有限公司

## TOLERANCE:

X.X ±0.30  
X.XX ±0.25  
X.XXX ±0.15  
X' ±2" X.X' ±0.5"

UNIT: mm [inch]

SCALE: 1:1

SIZE: A4

## DRAWN BY :

陈一鸣

## DATE :

2014-02-23

## PART NAME:

天线弹片 L1.80\*W1.50\*H2.40

## CHECKED BY:

马跃

## DATE :

2014-02-23

## PART NO.

HYCW-TXT181524A

## APPROVED BY:

邱敏

## DATE :

2014-02-23

## DRAW NO:

HYC-2412171629

## SHEET NO.

1 OF 1