







LOCK CARD TATUS



OPEN CARD TATUS



RECOMMENDED PCB LAYOUT(Top View)
GENERAL TOLERANCE ±0.05



MICRO SIM

PIN NO.	NAME	PIN NO.	NAME
C1	VCC	C4	VPP
C2	GND	C5	CLK
C3	RST	C6	IO

NOTES:

1. ELECTRICAL CHARACTERISTICS

- 1-1. CONTACT RESISTANCE: 60 Milliohms Max
- 1-2. INSULATION RESISTANCE: 1,000 Megohms Min.
- 1-3. VOLTAGE RATING: 50V.
- 1-4. CURRENT RATING: 1.0A.

2. MECHANICAL CHARACTERISTICS

- 2-1. OPERATION TEMPERATURE RANGE: -20°C~+85°C
- 2-2. DURABILITY: 5000 CYCLES

3. MATERIAL:

- 3-1. HOUSING: THERMOPLASTIC,UL 94-V0
- 3-2. TERMINAL: PHOSPHOR BRONZE,T=0.15mm
- 3-3. SHELL: STAINLESS STEEL,T=0.20mm

4. FINISHED:

- 4-1. TERMINAL: Ni PLATED UNDER, 1U" Au MIN PLATED

ON

CONTACT AREA,AU PLATED ON SOLDER TAIL

TAIL

- 4-2. SHELL: Ni PLATED UNDER,G/F PLATED ON SOLDER



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: MICRO SIM 6P 掀盖1.5H
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW298-SIM06-150B
	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2111161439
SCALE:1:1 SIZE: A4			SHEET NO. 1 OF 1