


TACT SWITCH



Operation: 立插式 中型 长寿命轻触开关 [操作力可定制]



ITEM NO.:TS-1104K-5507 (Series)

(L6.2mm×W6.2mm×H5.5mm TACT-SWITCH)

表面插装 DIP

正向操作 DOWN

精密部品 NICETY

可靠 STABILIZE

適合環保 RoHS

Technical parameter


LEVEL		A[better product]	B[average product]
PROJECT			
Electrical Properties	Contact Rating	0.25A, 24V DC	
	Initial Contact Resistance	50mΩ max.	
	Insulation Resistance	100MΩ min.500V DC Skey/PD: 100MΩ min.300V DC	
Durable Performance	Withstand Voltage	300V AC for 1 minute	250 V AC for 1 minut
	There No Load	3,000,000 Cycles	2,500,000 Cycles
	Rated Load	2,500,000 Cycles	2,000,000 Cycles
	Storage Temp	25℃/50℃RH (Operating temperature: -35℃~+75℃)	
	Operating Force	0.7 / 1.4N. (1N.=100gram-force)	
	Heat Rrsistance	IR Reflow:255℃, 5sec. Manual:350℃, 3sec.	

TS-1104K - XX XX

产品型号



操作力度
07=0.7N
14=1.4N
16=1.6N
26=2.6N

高度
43=4.3mm
50=5.0mm
55=5.5mm






Unit:mm

CIRCUIT DIAGRAM



Material declaration

No.	NAME	Description
① A	拨柄	POM(Black)耐温塑胶
② B	缓垫	软性硅胶 SILICA GEL
③ C	盖板	PBT
④ D	簧片	覆银&不锈钢 SUS304
⑤ E	基座	PA66(Black)耐高温尼龙
⑥ C	嵌件	C5191R-H (t=0.25mm)镀银磷铜



P.C.B LAYOUT

