








P.C.B LAYOUT

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 1.0
- 2.Voltage Rating: 50V AC DC
- 3.Current Rating: 1A AC DC
- 4.Insulation Resistance: 100MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 500V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

Part No	Pin	A	B	C
DSH-S02QCA-43	2	1.00	4.35	2.60
DSH-S03QCA-43	3	2.00	5.35	3.60
DSH-S04QCA-43	4	3.00	6.35	4.60
DSH-S05QCA-43	5	4.00	7.35	5.60
DSH-S06QCA-43	6	5.00	8.35	6.60
DSH-S07QCA-43	7	6.00	9.35	7.60
DSH-S08QCA-43	8	7.00	10.35	8.60
DSH-S09QCA-43	9	8.00	11.35	9.60
DSH-S10QCA-43	10	9.00	12.35	10.60
DSH-S11QCA-43	11	10.00	13.35	11.60
DSH-S12QCA-43	12	11.00	14.35	12.60
DSH-S13QCA-43	13	12.00	15.35	13.60
DSH-S14QCA-43	14	13.00	16.35	14.60
DSH-S15QCA-43	15	14.00	17.35	15.60
DSH-S16QCA-43	16	15.00	18.35	16.60
DSH-S20QCA-43	20	19.00	22.35	20.60

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X ±0.30	X.* ±5°	PART NO. DSH-SXQCA-43	TITLE: WAFER 1.00 贴片		
.XX ±0.20	X.* ±3°				
.XXX ±0.10	X.XX* ±1°				
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG		
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava			
				SCALE N:A	SHEET 1/1