




SUGGESTED PCB LAYOUT
(COMPONENT SIDE)



技术要求:

1. 塑件材料: PA66(UL-94V-0)
2. 接触件: 黄铜镀锡
3. 接触电阻: $\leq 10m\Omega$
4. 绝缘电阻: $\geq 100M\Omega$
5. 额定电压: 250V AC DC
6. 额定电流: 2.0A AC DC
7. 耐压: 能承受 1000V AC/Minute
8. 工作温度: $-25^{\circ}\sim+85^{\circ}$
9. 可焊性试验: 浸锡面积 $\geq 95\%$ 温度 $235\pm 5^{\circ}$, 时间 2.5 ± 0.5 秒
10. 铅和铜等六大有害物质含量要符合环保要求。

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Part No	Pin	A	B
AXH-2AW-11	2	2.50	7.50
AXH-3AW-11	3	5.00	10.00
AXH-4AW-11	4	7.50	12.50
AXH-5AW-11	5	10.00	15.00
AXH-6AW-11	6	12.50	17.50
AXH-7AW-11	7	15.00	20.00
AXH-8AW-11	8	17.50	22.50
AXH-9AW-11	9	20.00	25.00
AXH-10AW-11	10	22.50	27.50
AXH-11AW-11	11	25.00	30.00
AXH-12AW-11	12	27.50	32.50
AXH-13AW-11	13	30.00	35.00
AXH-14AW-11	14	32.50	37.50
AXH-15AW-11	15	35.00	40.00
AXH-16AW-11	16	37.50	42.50
AXH-17AW-11	17	40.00	45.00
AXH-18AW-11	18	42.50	47.50
AXH-19AW-11	19	45.00	50.00
AXH-20AW-11	20	47.50	52.50

2	端子Contact	黄铜	N*1	电镀(锡): 整个表面镀底镍 30u"MIN, 再镀锡80u"MIN
1	基座Wafer	PA66(UL94 V-0)	1	白色
序号	名称	材料	数量	备注

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X ±0.20	X.° ±10°	PART NO.		TITLE:	
.XX ±0.10	.X° ± 8°	AXH-XAW-11		XH2.54MM 弯针	
.XXX ±0.05	.XX° ± 5°	DESIGN: Ethan		MANUFACTURE DWG	
UNITS	mm	CHED: Olivia		 SCALE SHEET	
MATERILA	— — —	APPD: Ava			
FINISH	— — —			N:A	1/1