


REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

技术要求Specification:

- 1、材质Material: PA66 UL94V-0:
- 2、额定电流 Current rating:2.0A AC,DC
- 3、额定电压 Voltage rating:250V AC,DC
- 4、温度范围 Temperature range:-25℃to+85℃
- 5、接触电阻 Contact resistance:≤20mΩ
- 6、绝缘电阻Insulation resistance:≥1000MΩ
- 7、耐压Withstand voltage:500V AC/minute
- 8、塑件表面平整光洁,无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious glitches, bubbles, distortion, gate strain, lack of material and other undesirable phenomena.



Part No	Pin	A	B	C	D	E
CPAP-02V-JK	2	2.00	4.70	2.30	1.00	0.60
CPAP-03V-JK	3	4.00	6.70	2.30	1.00	0.60
CPAP-04V-JK	4	6.00	8.70	4.30	1.70	1.00
CPAP-05V-JK	5	8.00	10.70	4.30	1.70	1.00
CPAP-06V-JK	6	10.00	12.70	8.30	5.90	1.95
CPAP-07V-JK	7	12.00	14.70	10.30	7.90	1.95
CPAP-08V-JK	8	14.00	16.70	12.30	9.90	1.95
CPAP-09V-JK	9	16.00	18.70	12.30	9.90	1.95
CPAP-10V-JK	10	18.00	20.70	12.30	9.90	1.95
CPAP-11V-JK	11	20.00	22.70	16.30	13.90	1.95
CPAP-12V-JK	12	22.00	24.70	16.30	13.90	1.95
CPAP-13V-JK	13	24.00	26.70	16.30	13.90	1.95
CPAP-14V-JK	14	26.00	28.70	16.30	13.90	1.95
CPAP-15V-JK	15	28.00	30.70	16.30	13.90	1.95
CPAP-16V-JK	16	30.00	32.70	16.30	13.90	1.95

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X ±0.30	X.* ±1*	PART NO. CPAP-XV-JK	TITLE: HY2.0MM HOUSING		
.XX ±0.20			DESIGN: Ethan		
.XXX ±0.10			MANUFACTURE DWG		
UNITS	mm	CHED: Olvia	SCALE N:A	SHEET 1/1	
MATERILA	---	APPD: Ava			
FINISH	---				