


4

3

2

1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	05DEC2018	F.Z	R.B



RECOMMEND PC BOARD HOLE PATTERN
: CONNECTOR MOUNT SIDE (NOT ACCUMULATE TOLERANCE)
PC BOARD THICKNESS : 1.0~1.6±0.1

1. MATERIAL: HOUSING: GLASS FILLED THERMO PLASTIC
POLYESTER (94V-0), COLOR: BLACK
CONTACT: COPPER ALLOY
RETENTION LEG: Pre-Tin COPPER ALLOY
2. FINISH (ALL OVER): NICKEL PL. 1.27um MIN
3. FINISH (CONTACT OVER): TIN PL. 1.0um MIN AFTER 2
4. THE SHAPE, SIZE AND POSITION OF THE CHARACTER
SHOW THE OUTLINE.
THEY DON'T SHOW DETAILS.

P/N 1-2348456-2
(2P: X-KEY)

2	I	2.5	6.0	7.6	1-2348456-2
POS.	n	A	B	C	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
±0.3, ±3°

Ø PLC	±
1 PLC	±
2 PLC	±
3 PLC	±
4 PLC	±
ANGLES	±

MATERIAL

1

FINISH

2 3

DWN
FISHER.ZHU
05DEC2018

CHK
RICK.BIAN
05DEC2018

APVD
RICK.BIAN
05DEC2018

PRODUCT SPEC
108-78298

APPLICATION SPEC
114-5377

WEIGHT

RESTRICTED CUSTOMER

TE Connectivity

DYNAMIC D1200S 2.5mm PITCH
HDR ASSY, V-TYPE TIN PLATING
2 POS

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2348456	

SCALE	SHEET	OF	REV
6:1	1	1	A