





REV.	DESCRIPTION	DESIGN	APPROVAL	DATE
A0	NEW VERSION	Yuan	Jerry	2024.03.15

Specifications:
Contact resistance: $\leq 10\text{m}\Omega$;
Insulation resistance: $\geq 1000\text{M}\Omega$;
Rated voltage:250V AC/DC;
Rated current:5.0A AC/DC;
Withstand Voltage: 1000V AC/minute;
Temperature Range:-25°C~ +85°C;
Housing:LCP UL94V-0.BLACK;
Contacts:Brass/MATTE Sn-plated;
Solder Tabs:Brass/MATTE Sn-plated;

Part no:
991-XX X - X 1 1 0
Colour:1:White; 2:Black
Plating:1:Sn; 3:Au
No.of Poles:02~24

PART No.	Poles	Dimensions(mm)	
		A	B
991-021-2110	2x1	/	6.65
991-041-2110	2x2	3.00	9.65
991-061-2110	2x3	6.00	12.65
991-081-2110	2x4	9.00	15.65
991-101-2110	2x5	12.00	18.65
991-121-2110	2x6	15.00	21.65
991-141-2110	2x7	18.00	24.65
991-161-2110	2x8	21.00	27.65
991-181-2110	2x9	24.00	30.65
991-201-2110	2x10	27.00	33.65
991-221-2110	2x11	30.00	36.65
991-241-2110	2x12	33.00	39.65

X $\pm$ 0.50	X* $\pm$ 0.5°		Guangdong JiDe Precision Electronics Co., Ltd		
.X $\pm$ 0.30	.X* $\pm$ 0.3°		广东济德精密电子有限公司		
.XX $\pm$ 0.20	.XX* $\pm$ /		TITLE: 3.0Pitch Wafer 90°SMT		
.XXX $\pm$ 0.10	.XXX* $\pm$ /		PART NO. 991-XXX-X110		
UNITS:	mm		DWG NO: C-991-XXX-X110		
The information in this document is property of JIDCON company and should not be copied or reproduced in any other way, without written permission.			APPD:		
			CHKD:		
			DRAW:		
			SCALE	SHEET	REV.
			1:1	1/2	A0

