




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-		A	ECR-14-000387	10JAN2014	LW	PY
			A1	ECR-14-015136	10OCT2014	LW	PY
			A2	ECR-15-005723	13APR2015	KR	TD
			B	ECR-18-001422	26MAR2018	SG	SM

D



- 1 FLAT SEAL ASSEMBLED ON PIN HOUSING
- 2 NUT ENCLOSE LOOSELY
- 3 RECOMMENDED TIGHTENING TORQUE FOR NUT (ITEM NO.4)1.0-1.2Nm WHEN ASSEMBLING AT PANEL WALL
- 4 USE ONLY CRIMPING TOOL OF TE CONNECTIVITY TO CRIMP CONTACT.
A. CRIMPING TOOL PN 6-1579014-9 WILL BE USED FOR CRIMPING THE CONTACTS HAVING WIRE SIZE 2.5mm² and 4.0mm².
B. CRIMPING TOOL PN 6-1579014-8 WILL BE USED FOR CRIMPING THE CONTACTS HAVING WIRE SIZE 4.0mm² and 6.0mm².


C



SCALE 2:1

-1 AS SHOWN

B



RECOMMENDED MOUNTING HOLE

T(PANEL THICKNESS): 2-6mm
FEATURE A DETERMINED BY CUSTOMER

					PACKAGING		
	1-1971919-2	1-1971919-1	1971919-2	1971919-1	ORDER-NO.		
	1	1	-	-	PIN CONTACT, 2.5mm2/14AWG	4 A	5
-	-	-	1	1	PIN CONTACT, 4~6mm2/10~12AWG	4 B	
-	1	1	1	1	NUT M12x1.5	2	4
-	1	1	1	1	FLAT SEAL	1	3
-	1	1	1	1	METAL CLIP RING		2
-	1	1	1	1	PIN HOUSING		1
QUANTITY					DESCRIPTION	ITEM	

A

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

CHRIS WANG

28MAR2013

CHK

DANIEL TAO

28MAR2013

APVD

PETER YIN

28MAR2013

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.3

1 PLC ±0.3

2 PLC ±0.3

3 PLC ±0.3

4 PLC ±0.3

ANGLES ±

FINISH ±

PRODUCT SPEC

108-106122

APPLICATION SPEC

114-106122

WEIGHT

-

Customer Drawing

NAME

PIN CONNECTOR KITS

PV4 PANEL MOUNTED CONNECTOR

-

SIZE

A2

CAGE CODE

00779

DRAWING NO

1971919

RESTRICTED TO

-

SCALE

2:1

SHEET

1

OF

1

REV

B