

## Features

- Low On-resistance,  $R_{on}=10\Omega$
- 1.8V Logic Compatible Control Pin
- A Overrides VCC to Achieve True Isolation Even When Supply Is Dead
- High Off-isolation: -100dB @ 100KHz
- Low Channel-to-Channel Crosstalk: -97dB @ 100KHz
- High Bandwidth (-3dB @700MHz) Suitable For USB2.0 High-Speed Routing
- Low Quiescent Current (<2uA) With Very Wide Supply Range (1.5V ~ 5.5V)


## General Description

The is a low voltage single-pole,double-throw (SPDT) analog switch intending for use in chopping,modem, signal gating, and signal multiplexing for analog-to-digital and digital -to-analog conversion systems.

## PIN DESCRIPTION

PIN NO.	PIN NAME	DESCRIPTION
1	NO	Independent input or output
2	GND	Ground (0 V)
3	NC	Independent input or output
4	COM	Common output or input
5	V+	Supply voltage
6	IN	Select input


## Pin Configuration



## Applications

- Cell phones and TWS headset
- Audio, Video, UART, USB2.0 Signal and Supply Routing

## Logic Diagram



## Function Table

INPUT	OUTPUT
L	NC Connected to COM
H	NO Connected to COM

Note:H: HIGH voltage level;L: LOW voltage level.

## Absolute Maximum Ratings

(Unless otherwise specified)

PARAMETER	SYMBOL	RATINGS	UNIT
Supply Voltage	VCC	-0.3 ~ +6.5	V
Switch Voltage	V <sub>S</sub>	-0.3 ~ +6.5	V
Input Voltage	V <sub>IN</sub>	-0.3 ~ +6.5	V
Continuous Current Through COM, NO, NC		±128	mA
Peak Current Through COM, NO, NC (pulsed at 1ms 50% duty cycle)		±180	mA
Storage Temperature Range	T <sub>STG</sub>	-55 ~ +150	°C
Operating Junction Temperature	T <sub>J</sub>	150	°C
Junction to Ambient	R <sub>θJA</sub>	280	°C/W

Note: Absolute maximum ratings are those values beyond which the device could be permanently damaged.

Absolute maximum ratings are stress ratings only and functional device operation is not implied.

## Recommend operating ratings

(Unless otherwise specified)

PARAMETER	SYMBOL	RATINGS	UNIT
Supply Voltage Operating	VCC	1.5 ~ 5.5	V
Control Input Voltage	V <sub>SEL</sub>	-0.3 ~ 5.5	V
Input Signal Voltage	V <sub>A</sub>	-0.3 ~ 5.5	V
Operating Temperature	T <sub>A</sub>	-40 ~ +85	°C

**Electrical Characteristics ( TA =25°C, unless otherwise specified)**

PARAMETER	SYMBOL	TEST Conditions	MIN	TYP	MAX	UNIT
High-Level Input Voltage	V <sub>IH</sub>	V <sub>CC</sub> =3.3V ~ 5.5V	1.6	--	--	V
		V <sub>CC</sub> =1.5V ~ 3.3V	1.4	--	--	V
Low-Level Input Voltage	V <sub>IL</sub>	V <sub>CC</sub> =3.3V ~ 5.5V	--	--	0.6	V
		V <sub>CC</sub> =1.5V ~ 3.3V	--	--	0.4	V
Supply quiescent current	I <sub>CC</sub>	I <sub>A</sub> =0, V <sub>SEL</sub> =0 or V <sub>SEL</sub> =V <sub>CC</sub>	--	--	1.0	uA
Increase in ICC per input	I <sub>CC</sub> T	I <sub>A</sub> =0, V <sub>CC</sub> =4.5V V <sub>SEL</sub> >1.8 or V <sub>SEL</sub> <0.5	--	--	1.0	uA
Off state leakage from COM to NO (or NC)	I <sub>A</sub>	V <sub>A</sub> = 5.5V , V <sub>B0(or B1)</sub> = 0V	--	--	±2.0	uA
On-Resistance	R <sub>ON1</sub>	V <sub>A</sub> =0 ~ 0.5V, I <sub>A</sub> =30mA	--	5.6	10	Ω
	R <sub>ON2</sub>	V <sub>A</sub> =0.5 ~ 2.0V, I <sub>A</sub> =30mA	--	5.0	5.5	Ω
	R <sub>ON3</sub>	V <sub>A</sub> =2.0 ~ 4.0V, I <sub>A</sub> =30mA	--	4.5	5.5	Ω
	R <sub>ON4</sub>	V <sub>A</sub> =4.0 ~ 5.5V, I <sub>A</sub> =30mA	--	3.5	3.8	Ω
On-Resistance Flatness	R <sub>FLAT1</sub>	V <sub>A</sub> =0 ~ 0.5V, I <sub>A</sub> =30mA	--	1.6	--	Ω
	R <sub>FLAT2</sub>	V <sub>A</sub> =0.5 ~ 2.0V, I <sub>A</sub> =30mA	--	0.7	--	Ω
	R <sub>FLAT3</sub>	V <sub>A</sub> =2.0 ~ 4.0V, I <sub>A</sub> =30mA	--	0.5	--	Ω
	R <sub>FLAT4</sub>	V <sub>A</sub> =4.0 ~ 5.5V, I <sub>A</sub> =30mA	--	0.3	--	Ω
On-Resistance Matching Between Channels	Δ R <sub>ON</sub>	V <sub>A</sub> =0~5.5V, I <sub>A</sub> =30mA	--	0.1	0.2	Ω


**AC Electronics Characteristics (Ta=25°C, VCC=3.3V, unless otherwise noted)**

PARAMETER	SYMBOL	TEST Conditions	MIN	TYP	MAX	UNIT
Turn-On Time	T <sub>ON</sub>	V <sub>A</sub> =1.5V, C <sub>L</sub> =35pF, R <sub>L</sub> =50Ω	--	200	--	ns
Turn-Off Time	T <sub>OFF</sub>	V <sub>A</sub> =1.5V, C <sub>L</sub> =35pF, R <sub>L</sub> =50Ω	--	200	--	ns
Break-Before-Make time	T <sub>BBM</sub>	V <sub>A</sub> =1.5V, C <sub>L</sub> =35pF, R <sub>L</sub> =50Ω	--	500	--	ns
-3dB Bandwidth	BW	R <sub>L</sub> =50Ω, C <sub>L</sub> =0pF	--	700	--	MHz
Off isolation	OIRR	F=1KHz, R <sub>L</sub> =50Ω	--	-81	--	dB
		F=10KHz, R <sub>L</sub> =50Ω	--	-80	--	dB
Crosstalk	Xtalk	F=1KHz, R <sub>L</sub> =50Ω	--	-83	--	dB
		F=10KHz, R <sub>L</sub> =50Ω	--	-82	--	dB
Total Harmonic Distortion	THD	F=20Hz to 20KHz V <sub>A</sub> =600mVp-p @R <sub>L</sub> =32Ω	--	-80	--	dB


### Capacitance (Ta=25°C unless otherwise noted)

PARAMETER	SYMBOL	TEST Conditions	MIN	TYP	MAX	UNIT
Off capacitance	C <sub>OFF</sub>	F=100KHz, V <sub>CC</sub> =3.3	--	5.0	--	pF
On capacitance	C <sub>ON</sub>	F=100KHz, V <sub>CC</sub> =3.3	--	7.0	--	pF


### TEST CIRCUIT AND WAVEFORMS



TEST	S
t <sub>PLH</sub> /t <sub>PHL</sub>	Open
t <sub>PZH</sub> /t <sub>PZL</sub>	GND
t <sub>PLZ</sub> /t <sub>PZL</sub>	2 x V <sub>CC</sub>




Note: C<sub>L</sub> includes probe and jig capacitance.  
PRR ≤ 1MHz, Z<sub>O</sub> = 50Ω, t<sub>R</sub> ≤ 2.5ns, t<sub>F</sub> ≤ 2.5ns.



## Package information

SOT23-6 (Unit: mm)



## Mounting Pad Layout (unit: mm)

