




NOTES:

1. MATERIAL
HOUSING & P&P CAP : HIGH TEMPERATURE THERMOPLASTIC, UL94-V0; COLOR- BLACK
CONTACT PIN : COPPER ALLOY
FINISH :
MATING SIDE: MIN. 0.38 μ m GOLD OVER NICKEL UNDER PLATING.
SOLDER SIDE: MIN. 2.0 μ m BRIGHT TIN OVER NICKEL UNDER PLATING.
2. PACKAGING: TUBE (WITH PICK AND PLACE CAP).
3. TOLERANCE NOT CUMULATIVE.
4. CUTTING BURR MAX. 0.25 mm.




RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE WAVE



RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE REFLOW / PIN-IN-PASTE

1-2355179-0 AS SHOWN



48.0	50.0	25	2-2355179-5
46.0	48.0	24	2-2355179-4
44.0	46.0	23	2-2355179-3
42.0	44.0	22	2-2355179-2
40.0	42.0	21	2-2355179-1
38.0	40.0	20	2-2355179-0
36.0	38.0	19	1-2355179-9
34.0	36.0	18	1-2355179-8
32.0	34.0	17	1-2355179-7
30.0	32.0	16	1-2355179-6
28.0	30.0	15	1-2355179-5
26.0	28.0	14	1-2355179-4
24.0	26.0	13	1-2355179-3
22.0	24.0	12	1-2355179-2
20.0	22.0	11	1-2355179-1
18.0	20.0	10	1-2355179-0
16.0	18.0	9	2355179-9
14.0	16.0	8	2355179-8
12.0	14.0	7	2355179-7
10.0	12.0	6	2355179-6
8.0	10.0	5	2355179-5
6.0	8.0	4	2355179-4
DIM "F"	DIM "E"	POS	TE PN

PICK AND PLACE CAP	3
CONTACT PIN	2
HOUSING	1
DESCRIPTION	ITEM NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA.K	09APR2019				TE Connectivity	
		CHK KARTHIK.JK	14AUG2019					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD PRASHANTH	NAME AMPMODU 2mm BREAKAWAY HEADER			
		0 PLC ± 1 PLC ±0.2 2 PLC ±0.15 3 PLC ± 4 PLC ±		PRODUCT SPEC 108-64040	SINGLE ROW, VERTICAL, 0.38 Au, TUBE, PICK AND PLACE CAP			
		ANGLES ±°		APPLICATION SPEC 114-32259	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
MATERIAL SEE NOTES	FINISH SEE NOTES	WEIGHT -		A2	00779	C=2355179		-
CUSTOMER DRAWING					SCALE	10:1	SHEET	1 OF 1 REV B