

Features


- Programmable Precise Output Voltage from 2.5V to 36V
- High Stability under Capacitive Load
- Low Temperature Deviation: 4.5mV Typical
- Low Equivalent Full-range Temperature Coefficient with 20PPM/°C Typical
- Sink Current Capacity from 1mA to 100mA
- Low Output Noise
- Wide Operating Range of -40 to +125°C

Application

- Shunt Regulator
- High-Current Shunt Regulator
- Precision Current Limiter


Description

The TL431 is a three-terminal adjustable shunt regulator with guaranteed thermal stability over a full operation range. It features sharp turn-on characteristics, low temperature coefficient and low output impedance, which make it ideal substitute for Zener diode in applications such as switching power supply, charger and other adjustable regulators.




Equivalent Circuit


Typical Applications Circuit




Shunt Regulator




High Current Shunt Regulator



Current Source or Current Limit




Precision 5V 1A Regulator




PWM Converter with Reference

Functional Block Diagram



Packages And Pin Assignment



Pin No.	Pin Name	Pin Description
SOT-23		
1	R	Reference pin
3	A	Anode pin
2	K	Cathode pin

Absolute Maximum Ratings

Symbol	Parameter	Value			Unit
		SOT-23	SOT-89	TO-92	
V_{KA}	Cathode Voltage	40			V
I_{KA}	Cathode Current Range (Continuous)	-100~+150			mA
I_{REF}	Reference Input Current Range	0.05~+10			mA
P_D	Power Dissipation	300	500	770	mW
$R_{\theta JA}$	Thermal Resistance from Junction to Ambient	380	165	165	°C/W
T_J	Operating Junction Temperature	-40~+125			°C
T_{STG}	Storage Temperature Range	-65~150			°C
ESD	ESD (Human Body Model)	2000			V

Note: Stresses greater than those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "Recommended Operating Conditions" is not implied. Exposure to "Absolute Maximum Ratings" for extended periods may affect device reliability.


Recommended Operating Conditions

Symbol	Parameter	Min	Max	Unit
V_{KA}	Cathode Voltage	V_{REF}	36	V
I_{KA}	Cathode Current	1.0	100	mA
T_A	Operating Junction Temperature Range	-40	125	°C


Electrical Characteristics

Symbol	Parameter	Test Conditions	Min	Typ	Max	Unit
V_{REF}	Reference Input Voltage	$V_{KA}=V_{REF}, I_{KA}=10mA$	0.40%	2.49	2.51	V
			0.80%	2.48	2.52	V
ΔV_{REF}	Deviation of Reference Voltage Over Full Temperature Range	$V_{KA}=V_{REF}, I_{KA}=10mA$	0~+70°C	-	4.50	8.0 mV
			-40~+85°C	-	4.80	10.0 mV
			-40~+125°C	-	4.50	16.0 mV
$\Delta V_{REF}/\Delta V_{KA}$	Ratio of change in reference input voltage to the change in cathode voltage	$I_{KA}=10mA$	$\Delta V_{KA}=10V-V_{REF}$	-	-1.0	-2.7 mV/V
			$\Delta V_{KA}=36V-10V$	-	-0.50	-2.0 mV/V
I_{REF}	Reference Input Current	$I_{KA}=10mA, R1=10K\Omega, R2=\infty$	-	0.70	4.0	uA
ΔI_{REF}	Deviation of reference input current over full temperature range	$I_{KA}=10mA, R1=10K\Omega, R2=\infty, T_A=-40$ to +125°C	-	0.40	1.2	uA
$I_{KA} (Min)$	Minimum Cathode Current for Regulation	$V_{KA}=V_{REF}$	-	0.40	1.0	mA
$I_{KA} (Off)$	Off-state Cathode Current	$V_{KA}=36V, V_{REF}=0$	-	0.05	1.0	uA
Z_{KA}	Dynamic Impedance	$V_{KA}=V_{REF}, I_{KA}=1$ to 100mA, $f \leq 1.0kHz$	-	0.15	0.5	Ω
θ_{JC}	Thermal Resistance	SOT-23	-	135.48	-	°C/W
		TO-92	-	81.63	-	°C/W
		SOT-89	-	29.80	-	°C/W


Electrical Characteristics(Cont.)



Test Circuit 4 for $V_{KA} = V_{REF}$





Test Circuit 5 for $V_{KA} > V_{REF}$



Test Circuit 6 for I_{OFF}



Performance Characteristics(Cont.)

Pulse Response of Input and Output Voltage





Performance Characteristics(Cont.)



Small Signal Voltage Gain vs. Frequency




Reference Impedance vs. Frequency



Stability Boundary Conditions vs. Load Capacitance



Package Outline Dimensions: SOT-23



DIMENSIONS

SYMBOL	MILLIMETER		INCHES	
	MIN	MAX	MIN	MAX
A	0.900	1.150	0.035	0.045
A1	0.000	0.100	0.000	0.004
A2	0.900	1.050	0.035	0.041
D	2.800	3.000	0.110	0.118
b	0.300	0.500	0.012	0.020
E	2.250	2.550	0.089	0.100
E1	1.200	1.400	0.047	0.055
e	0.950 BSC		0.037 BSC	
L	0.300	0.500	0.012	0.020
θ	0	8°	0	8°