



**BLZP 5.00HC/08/180 SN GN BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Female plug with clamping-yoke screw system for connecting wires with straight (180°) outlet direction. The female connectors provide space for labelling and can be coded. Fastened by means of a flange or release latch. They also provide an integrated plus/minus screw, protection against faulty insertion of the wire, and they are delivered with open clamping yokes. HC = High Current.

**General ordering data**

|              |                                                                                                                                   |
|--------------|-----------------------------------------------------------------------------------------------------------------------------------|
| Version      | PCB plug-in connector, female plug, 5.00 mm, Number of poles: 8, 180°, Clamping yoke connection, Clamping range, max.: 4 mm², Box |
| Order No.    | <a href="#">1205030000</a>                                                                                                        |
| Type         | BLZP 5.00HC/08/180 SN GN BX                                                                                                       |
| GTIN (EAN)   | 4032248987481                                                                                                                     |
| Qty.         | 42 pc(s).                                                                                                                         |
| Product data | IEC: 400 V / 23 A / 0.2 - 4 mm²<br>UL: 300 V / 20 A / AWG 26 - AWG 12                                                             |
| Packaging    | Box                                                                                                                               |

Creation date October 11, 2022 7:13:31 PM CEST

**BLZP 5.00HC/08/180 SN GN BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 20.1 mm | Depth (inches)  | 0.791 inch |
| Height     | 16 mm   | Height (inches) | 0.63 inch  |
| Width      | 40 mm   | Width (inches)  | 1.575 inch |
| Net weight | 11.5 g  |                 |            |

**System Parameters**

|                                              |                                        |  |                   |      |        |
|----------------------------------------------|----------------------------------------|--|-------------------|------|--------|
| Product family                               | OMNIMATE Signal - series BL/SL 5.00    |  |                   |      |        |
| Type of connection                           | Field connection                       |  |                   |      |        |
| Wire connection method                       | Clamping yoke connection               |  |                   |      |        |
| Pitch in mm (P)                              | 5 mm                                   |  |                   |      |        |
| Pitch in inches (P)                          | 0.197 inch                             |  |                   |      |        |
| Conductor outlet direction                   | 180°                                   |  |                   |      |        |
| Number of poles                              | 8                                      |  |                   |      |        |
| L1 in mm                                     | 35 mm                                  |  |                   |      |        |
| L1 in inches                                 | 1.379 inch                             |  |                   |      |        |
| Number of rows                               | 1                                      |  |                   |      |        |
| Pin series quantity                          | 1                                      |  |                   |      |        |
| Rated cross-section                          | 4 mm²                                  |  |                   |      |        |
| Touch-safe protection acc. to DIN VDE 57 106 | Safe from finger touch                 |  |                   |      |        |
| Protection degree                            | IP20                                   |  |                   |      |        |
| Volume resistance                            | ≤5 mΩ                                  |  |                   |      |        |
| Can be coded                                 | Yes                                    |  |                   |      |        |
| Stripping length                             | 7 mm                                   |  |                   |      |        |
| Clamping screw                               | M 2.5                                  |  |                   |      |        |
| Screwdriver blade                            | 0.6 x 3.5, PH 1, PZ 1                  |  |                   |      |        |
| Screwdriver blade standard                   | DIN 5264, ISO 8764/2-PH, ISO 8764/2-PZ |  |                   |      |        |
| Plugging cycles                              | 25                                     |  |                   |      |        |
| Plugging force/pole, max.                    | 10 N                                   |  |                   |      |        |
| Pulling force/pole, max.                     | 9 N                                    |  |                   |      |        |
| Tightening torque                            | Torque type                            |  | Wire connection   |      |        |
|                                              | Usage information                      |  | Tightening torque | min. | 0.4 Nm |
|                                              |                                        |  |                   | max. | 0.5 Nm |

**Material data**

|                                       |          |                                       |                            |
|---------------------------------------|----------|---------------------------------------|----------------------------|
| Insulating material                   | PBT      | Colour                                | Pale green                 |
| Colour chart (similar)                | RAL 6021 | Insulating material group             | IIIa                       |
| Comparative Tracking Index (CTI)      | ≥ 200    | Insulation strength                   | ≥ 10 <sup>8</sup> Ω        |
| UL 94 flammability rating             | V-0      | Contact material                      | Copper alloy               |
| Contact surface                       | tinned   | Layer structure of plug contact       | 4...8 µm Sn hot-dip tinned |
| Storage temperature, min.             | -40 °C   | Storage temperature, max.             | 70 °C                      |
| Operating temperature, min.           | -50 °C   | Operating temperature, max.           | 100 °C                     |
| Temperature range, installation, min. | -25 °C   | Temperature range, installation, max. | 100 °C                     |

**Conductors suitable for connection**

|                                         |                      |
|-----------------------------------------|----------------------|
| Clamping range, min.                    | 0.13 mm <sup>2</sup> |
| Clamping range, max.                    | 4 mm <sup>2</sup>    |
| Wire connection cross section AWG, min. | AWG 30               |
| Wire connection cross section AWG, max. | AWG 12               |
| Solid, min. H05(07) V-U                 | 0.2 mm <sup>2</sup>  |

Creation date October 11, 2022 7:13:31 PM CEST

**BLZP 5.00HC/08/180 SN GN BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data**

|                                                                     |                                                                                                                                                                        |                              |                         |      |
|---------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------|-------------------------|------|
| Solid, max. H05(07) V-U                                             | 4 mm <sup>2</sup>                                                                                                                                                      |                              |                         |      |
| Stranded, min. H07V-R                                               | 0.2 mm <sup>2</sup>                                                                                                                                                    |                              |                         |      |
| Stranded, max. H07V-R                                               | 4 mm <sup>2</sup>                                                                                                                                                      |                              |                         |      |
| Flexible, min. H05(07) V-K                                          | 0.2 mm <sup>2</sup>                                                                                                                                                    |                              |                         |      |
| Flexible, max. H05(07) V-K                                          | 4 mm <sup>2</sup>                                                                                                                                                      |                              |                         |      |
| w. plastic collar ferrule, DIN 46228 pt 4, 0.2 mm <sup>2</sup> min. |                                                                                                                                                                        |                              |                         |      |
| w. plastic collar ferrule, DIN 46228 pt 4, 2.5 mm <sup>2</sup> max. |                                                                                                                                                                        |                              |                         |      |
| w. wire end ferrule, DIN 46228 pt 1, min.                           | 0.2 mm <sup>2</sup>                                                                                                                                                    |                              |                         |      |
| w. wire end ferrule, DIN 46228 pt 1, max.                           | 2.5 mm <sup>2</sup>                                                                                                                                                    |                              |                         |      |
| Plug gauge in accordance with EN 60999 a x b; ø                     | 2.8 mm x 2.4 mm                                                                                                                                                        |                              |                         |      |
| Clampable conductor                                                 | Cross-section for conductor connection                                                                                                                                 | Type                         | fine-wired              |      |
|                                                                     |                                                                                                                                                                        | nominal                      | 0.5 mm <sup>2</sup>     |      |
|                                                                     | wire end ferrule                                                                                                                                                       | Stripping length             | nominal                 | 6 mm |
|                                                                     |                                                                                                                                                                        | Recommended wire-end ferrule | <a href="#">H0.5/6</a>  |      |
|                                                                     | Cross-section for conductor connection                                                                                                                                 | Type                         | fine-wired              |      |
|                                                                     |                                                                                                                                                                        | nominal                      | 1 mm <sup>2</sup>       |      |
|                                                                     | wire end ferrule                                                                                                                                                       | Stripping length             | nominal                 | 6 mm |
|                                                                     |                                                                                                                                                                        | Recommended wire-end ferrule | <a href="#">H1.0/6</a>  |      |
|                                                                     | Cross-section for conductor connection                                                                                                                                 | Type                         | fine-wired              |      |
|                                                                     |                                                                                                                                                                        | nominal                      | 1.5 mm <sup>2</sup>     |      |
|                                                                     | wire end ferrule                                                                                                                                                       | Stripping length             | nominal                 | 7 mm |
|                                                                     |                                                                                                                                                                        | Recommended wire-end ferrule | <a href="#">H1.5/7</a>  |      |
|                                                                     | Cross-section for conductor connection                                                                                                                                 | Type                         | fine-wired              |      |
|                                                                     |                                                                                                                                                                        | nominal                      | 2.5 mm <sup>2</sup>     |      |
|                                                                     | wire end ferrule                                                                                                                                                       | Stripping length             | nominal                 | 7 mm |
|                                                                     |                                                                                                                                                                        | Recommended wire-end ferrule | <a href="#">H2.5/7</a>  |      |
|                                                                     | Cross-section for conductor connection                                                                                                                                 | Type                         | fine-wired              |      |
|                                                                     |                                                                                                                                                                        | nominal                      | 0.75 mm <sup>2</sup>    |      |
|                                                                     | wire end ferrule                                                                                                                                                       | Stripping length             | nominal                 | 6 mm |
|                                                                     |                                                                                                                                                                        | Recommended wire-end ferrule | <a href="#">H0.75/6</a> |      |
| Reference text                                                      | The outside diameter of the plastic collar should not be larger than the pitch (P), Length of ferrules is to be chosen depending on the product and the rated voltage. |                              |                         |      |

**Rated data acc. to IEC**

|                                                                           |                        |                                                                       |                   |
|---------------------------------------------------------------------------|------------------------|-----------------------------------------------------------------------|-------------------|
| tested acc. to standard                                                   | IEC 60664-1, IEC 61984 | Rated current, min. number of poles (Tu=20°C)                         | 23 A              |
| Rated current, max. number of poles (Tu=20°C)                             | 18 A                   | Rated current, min. number of poles (Tu=40°C)                         | 21 A              |
| Rated current, max. number of poles (Tu=40°C)                             | 16 A                   | Rated voltage for surge voltage class / pollution degree II/2         | 400 V             |
| Rated voltage for surge voltage class / pollution degree III/2            | 320 V                  | Rated voltage for surge voltage class / pollution degree III/3        | 250 V             |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 4 kV                   | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 4 kV              |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 4 kV                   | Short-time withstand current resistance                               | 3 x 1s with 120 A |

**BLZP 5.00HC/08/180 SN GN BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Rated data acc. to CSA**

|                                   |        |                                   |        |
|-----------------------------------|--------|-----------------------------------|--------|
| Rated voltage (Use group B / CSA) | 300 V  | Rated voltage (Use group C / CSA) | 50 V   |
| Rated voltage (Use group D / CSA) | 300 V  | Rated current (Use group B / CSA) | 20 A   |
| Rated current (Use group D / CSA) | 20 A   | Wire cross-section, AWG, min.     | AWG 30 |
| Wire cross-section, AWG, max.     | AWG 12 |                                   |        |

**Packing**

|           |        |            |        |
|-----------|--------|------------|--------|
| Packaging | Box    | VPE length | 338 mm |
| VPE width | 130 mm | VPE height | 27 mm  |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002638    | ETIM 7.0    | EC002638    |
| ETIM 8.0    | EC002638    | ECLASS 9.0  | 27-44-03-09 |
| ECLASS 9.1  | 27-44-03-09 | ECLASS 10.0 | 27-44-03-09 |
| ECLASS 11.0 | 27-46-02-02 | ECLASS 12.0 | 27-46-02-02 |

**Important note**

|                |                                                                                                                                                                                                                                                                                                                            |
|----------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| IPC conformity | Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request. |
|----------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

## Notes

- Additional variants on request
- Gold-plated contact surfaces on request
- Rated current related to rated cross-section & min. No. of poles.
- Wire end ferrule without plastic collar to DIN 46228/1
- Wire end ferrule with plastic collar to DIN 46228/4
- P on drawing = pitch
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.
- Long term storage of the product with average temperature of 50 °C and average humidity 70%, 36 months

**Approvals**

## Approvals



|                         |            |
|-------------------------|------------|
| ROHS                    | Conform    |
| UL File Number Search   | UL Website |
| Certificate No. (cURus) | E60693     |

**BLZP 5.00HC/08/180 SN GN BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

|                  |                                                              |
|------------------|--------------------------------------------------------------|
| Engineering Data | <a href="#">CAD data – STEP</a>                              |
| Catalogues       | <a href="#">Catalogues in PDF-format</a>                     |
| Brochures        | <a href="#">FL DRIVES EN</a><br><a href="#">FL DRIVES DE</a> |

## BLZP 5.00HC/08/180 SN GN BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Product image

