


1.0SMBJ / 1.0HSMBJ Series

Transient
Voltage Suppressor

Features

- Excellent clamping capability
- Low leakage current
- Low capacitance
- High surge capability
- Glass passivated chip
- Epoxy resin package
- Built-in strain relief
- Will not fatigue
- RoHS Compliant
- “H” Prefix is for Automotive applications, AEC-Q101 qualified

Package





Mechanical Characteristics

- Package: SMB plastic package
- Lead Finish: Matte Tin
- Case Material: Epoxy Molding Compound
- UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020

Applications

- Telecom
- Computer
- Industrial electronic
- Consumer electronic
- Automotive electronic

Making Code



Summary of Packing Options

Package	Packing Description	Packing Quantity	Industry Standard
SMB	Tape/Reel, 13" reel	3000	EIA-481-1
	Tape/Reel, 7" reel	500	EIA-481-1




1.0SMBJ / 1.0HSMBJ Series

Transient
Voltage Suppressor

Electrical Parameters

Parameter	Definition
C_J	Junction Capacitance - typical capacitance measured with 0V or V_R bias
I_{PP}	Peak Pulse Current - maximum rated peak impulse current
V_C	Clamping Voltage - Peak voltage measured across the suppressor at a specified I_{ppm}
V_{BR}	Breakdown Voltage - Maximum voltage that flows though the TVS at a specified test current (I_T)
I_R	Leakage Current - maximum peak off-state current measured at V_R
V_R	Peak Off-state Voltage - maximum voltage that can be applied while maintaining off state



Absolute Maximum Ratings ($T_A=+25^{\circ}\text{C}$, unless otherwise noted)

Parameter	Symbol	Value	Units
Peak Pulse Power Dissipation (Note1,2)	P_{PPM}	1000	W
Steady State Power Dissipation (Note3)	P_D	5	W
Peak Forward Surge Current (Note4)	I_{FSM}	150	A
Maximum Instantaneous Forward Voltage at 50A (Note5)	V_{FM}	3.5/5	V
Typical Thermal Resistance Junction to Lead	$R_{\theta JL}$	20	$^{\circ}\text{C/W}$
Typical Thermal Resistance Junction to Ambient	$R_{\theta JA}$	100	$^{\circ}\text{C/W}$
Operating Temperature Range	T_J	-55 to 150	$^{\circ}\text{C}$
Storage Temperature Range	T_{STG}	-55 to 150	$^{\circ}\text{C}$

Notes:

- (1) Non-repetitive current pulse , 10/1000us Waveform.
- (2) Mounted on copper pad area of 5×5mm to each terminal.
- (3) Infinite HeatSink at $T_A = 50^{\circ}\text{C}$
- (4) Measured on 8.3ms single half sine wave or equivalent square wave, duty cycle=4 perminute maximum.
- (5) For UnidirectionalOnly, $V_{FW} < 3.5\text{V}$ for $V_{BR} \leq 200\text{V}$ and $V_{FM} < 5.0\text{V}$ for $V_{BR} \geq 201\text{V}$.



1.0SMBJ / 1.0HSMBJ Series

Transient
Voltage Suppressor

Electrical Characteristics (T_A=+25°C, unless otherwise noted)

Part Number	Part Number	Reverse Stand-Off Voltage	Breakdown Voltage V _{BR} @I _T		Test Current I _T	Maximum Clamping Voltage V _C @ I _{pp}	Maximum Peak Pulse Current I _{pp}	Maximum Reverse Leakage I _R @ V _R
(Uni)	(Bi)	(V)	Min.(V)	Max.(V)	(mA)	(V)	(A)	(uA)
1.0SMBJ5.0A 1.0HSMBJ5.0A	1.0SMBJ5.0CA 1.0HSMBJ5.0CA	5	6.4	7	10	9.2	108.7	800
1.0SMBJ6.0A 1.0HSMBJ6.0A	1.0SMBJ6.0CA 1.0HSMBJ6.0CA	6	6.67	7.37	10	10.3	97.1	800
1.0SMBJ6.5A 1.0HSMBJ6.5A	1.0SMBJ6.5CA 1.0HSMBJ6.5CA	6.5	7.22	7.98	10	11.2	89.3	500
1.0SMBJ7.0A 1.0HSMBJ7.0A	1.0SMBJ7.0CA 1.0HSMBJ7.0CA	7	7.78	8.6	10	12	83.3	200
1.0SMBJ7.5A 1.0HSMBJ7.5A	1.0SMBJ7.5CA 1.0HSMBJ7.5CA	7.5	8.33	9.21	1	12.9	77.5	100
1.0SMBJ8.0A 1.0HSMBJ8.0A	1.0SMBJ8.0CA 1.0HSMBJ8.0CA	8	8.89	9.83	1	13.6	73.5	50
1.0SMBJ8.5A 1.0HSMBJ8.5A	1.0SMBJ8.5CA 1.0HSMBJ8.5CA	8.5	9.44	10.4	1	14.4	69.4	20
1.0SMBJ9.0A 1.0HSMBJ9.0A	1.0SMBJ9.0CA 1.0HSMBJ9.0CA	9	10	11.1	1	15.4	64.9	10
1.0SMBJ10A 1.0HSMBJ10A	1.0SMBJ10CA 1.0HSMBJ10CA	10	11.1	12.3	1	17	58.8	5
1.0SMBJ11A 1.0HSMBJ11A	1.0SMBJ11CA 1.0HSMBJ11CA	11	12.2	13.5	1	18.2	54.9	1
1.0SMBJ12A 1.0HSMBJ12A	1.0SMBJ12CA 1.0HSMBJ12CA	12	13.3	14.7	1	19.9	50.3	1
1.0SMBJ13A 1.0HSMBJ13A	1.0SMBJ13CA 1.0HSMBJ13CA	13	14.4	15.9	1	21.5	46.5	1
1.0SMBJ14A 1.0HSMBJ14A	1.0SMBJ14CA 1.0HSMBJ14CA	14	15.6	17.2	1	23.2	43.1	1
1.0SMBJ15A 1.0HSMBJ15A	1.0SMBJ15CA 1.0HSMBJ15CA	15	16.7	18.5	1	24.4	41.0	1
1.0SMBJ16A 1.0HSMBJ16A	1.0SMBJ16CA 1.0HSMBJ16CA	16	17.8	19.7	1	26	38.5	1
1.0SMBJ17A 1.0HSMBJ17A	1.0SMBJ17CA 1.0HSMBJ17CA	17	18.9	20.9	1	27.6	36.2	1
1.0SMBJ18A 1.0HSMBJ18A	1.0SMBJ18CA 1.0HSMBJ18CA	18	20	22.1	1	29.2	34.2	1

**BORN SEMICONDUCTOR, INC. ALL
RIGHT RESERVED**

Specifications are subject to change without notice.

Please refer to <http://www.born-tw.com> for current information.

Revision: 2022-Jan-1-A



1.0SMBJ / 1.0HSMBJ Series

Transient
Voltage Suppressor

Electrical Characteristics (T_A=+25°C, unless otherwise noted)

Part Number	Part Number	Reverse Stand-Off Voltage	Breakdown Voltage V _{BR} @I _T		Test Current I _T	Maximum Clamping Voltage V _C @ I _{pp}	Maximum Peak Pulse Current I _{pp}	Maximum Reverse Leakage I _R @ V _R
(Uni)	(Bi)	(V)	Min.(V)	Max.(V)	(mA)	(V)	(A)	(uA)
1.0SMBJ20A 1.0HSMBJ20A	1.0SMBJ20CA 1.0HSMBJ20CA	20	22.2	24.5	1	32.4	30.9	1
1.0SMBJ22A 1.0HSMBJ22A	1.0SMBJ22CA 1.0HSMBJ22CA	22	24.4	26.9	1	35.5	28.2	1
1.0SMBJ24A 1.0HSMBJ24A	1.0SMBJ24CA 1.0HSMBJ24CA	24	26.7	29.5	1	38.9	25.7	1
1.0SMBJ26A 1.0HSMBJ26A	1.0SMBJ26CA 1.0HSMBJ26CA	26	28.9	31.9	1	42.1	23.8	1
1.0SMBJ28A 1.0HSMBJ28A	1.0SMBJ28CA 1.0HSMBJ28CA	28	31.1	34.4	1	45.4	22.0	1
1.0SMBJ30A 1.0HSMBJ30A	1.0SMBJ30CA 1.0HSMBJ30CA	30	33.3	36.8	1	48.4	20.7	1
1.0SMBJ33A 1.0HSMBJ33A	1.0SMBJ33CA 1.0HSMBJ33CA	33	36.7	40.6	1	53.3	18.8	1
1.0SMBJ36A 1.0HSMBJ36A	1.0SMBJ36CA 1.0HSMBJ36CA	36	40	44.2	1	58.1	17.2	1
1.0SMBJ40A 1.0HSMBJ40A	1.0SMBJ40CA 1.0HSMBJ40CA	40	44.4	49.1	1	64.5	15.5	1
1.0SMBJ43A 1.0HSMBJ43A	1.0SMBJ43CA 1.0HSMBJ43CA	43	47.8	52.8	1	69.4	14.4	1
1.0SMBJ45A 1.0HSMBJ45A	1.0SMBJ45CA 1.0HSMBJ45CA	45	50	55.3	1	72.7	13.8	1
1.0SMBJ48A 1.0HSMBJ48A	1.0SMBJ48CA 1.0HSMBJ48CA	48	53.3	58.9	1	77.4	12.9	1
1.0SMBJ51A 1.0HSMBJ51A	1.0SMBJ51CA 1.0HSMBJ51CA	51	56.7	62.7	1	82.4	12.1	1
1.0SMBJ54A 1.0HSMBJ54A	1.0SMBJ54CA 1.0HSMBJ54CA	54	60	66.3	1	87.1	11.5	1
1.0SMBJ58A 1.0HSMBJ58A	1.0SMBJ58CA 1.0HSMBJ58CA	58	64.4	71.2	1	93.6	10.7	1
1.0SMBJ60A 1.0HSMBJ60A	1.0SMBJ60CA 1.0HSMBJ60CA	60	66.7	73.7	1	96.8	10.3	1
1.0SMBJ64A 1.0HSMBJ64A	1.0SMBJ64CA 1.0HSMBJ64CA	64	71.1	78.6	1	103	9.7	1

**BORN SEMICONDUCTOR, INC. ALL
RIGHT RESERVED**

Specifications are subject to change without notice.

Please refer to <http://www.born-tw.com> for current information.

Revision: 2022-Jan-1-A



1.0SMBJ / 1.0HSMBJ Series

Transient
Voltage Suppressor

Electrical Characteristics (T_A=+25°C, unless otherwise noted)

Part Number	Part Number	Reverse Stand-Off Voltage	Breakdown Voltage V _{BR} @I _T		Test Current I _T	Maximum Clamping Voltage V _C @ I _{pp}	Maximum Peak Pulse Current I _{pp}	Maximum Reverse Leakage I _R @ V _R
(Uni)	(Bi)	(V)	Min.(V)	Max.(V)	(mA)	(V)	(A)	(uA)
1.0SMBJ64A 1.0HSMBJ64A	1.0SMBJ64CA 1.0HSMBJ64CA	64	71.1	78.6	1	103	9.7	1
1.0SMBJ70A 1.0HSMBJ70A	1.0SMBJ70CA 1.0HSMBJ70CA	70	77.8	86	1	113	8.8	1
1.0SMBJ75A 1.0HSMBJ75A	1.0SMBJ75CA 1.0HSMBJ75CA	75	83.3	92.1	1	121	8.3	1
1.0SMBJ78A 1.0HSMBJ78A	1.0SMBJ78CA 1.0HSMBJ78CA	78	86.7	95.8	1	126	7.9	1
1.0SMBJ85A 1.0HSMBJ85A	1.0SMBJ85CA 1.0HSMBJ85CA	85	94.4	104	1	137	7.3	1
1.0SMBJ90A 1.0HSMBJ90A	1.0SMBJ90CA 1.0HSMBJ90CA	90	100	111	1	146	6.8	1
1.0SMBJ100A 1.0HSMBJ100A	1.0SMBJ100CA 1.0HSMBJ100CA	100	111	123	1	162	6.2	1
1.0SMBJ110A 1.0HSMBJ110A	1.0SMBJ110CA 1.0HSMBJ110CA	110	122	135	1	177	5.6	1
1.0SMBJ120A 1.0HSMBJ120A	1.0SMBJ120CA 1.0HSMBJ120CA	120	133	147	1	193	5.2	1
1.0SMBJ130A 1.0HSMBJ130A	1.0SMBJ130CA 1.0HSMBJ130CA	130	144	159	1	209	4.8	1
1.0SMBJ150A 1.0HSMBJ150A	1.0SMBJ150CA 1.0HSMBJ150CA	150	167	185	1	243	4.1	1
1.0SMBJ160A 1.0HSMBJ160A	1.0SMBJ160CA 1.0HSMBJ160CA	160	178	197	1	259	3.9	1
1.0SMBJ170A 1.0HSMBJ170A	1.0SMBJ170CA 1.0HSMBJ170CA	170	189	209	1	275	3.6	1



1.0SMBJ / 1.0HSMBJ Series

Transient
Voltage Suppressor

Ratings and Characteristic Curves ($T_A = +25^\circ\text{C}$, unless otherwise noted)

Figure 1: Peak Pulse Power Rating




Figure 2: Pulse Derating Curve




Figure 3: Pulse Waveform




Figure 4: Typical Junction Capacitance




Figure 5: Steady State Power Dissipation Derating

Curve






Figure 6: Maximum Non-Repetitive Peak Forward

Surge Current Uni-Directional Only



Soldering Parameters




Reflow Condition		Lead-free assembly
Pre Heat	- Temperature Min ($T_{S(min)}$)	150°C
	- Temperature Max ($T_{S(max)}$)	200°C
	- Time (min to max) (t_s)	60 - 180 secs
Average ramp up rate (Liquidus Temp (T_L) to peak)		3°C/second max
$T_{S(max)}$ to T_L - Ramp-up Rate		3°C/second max
Reflow	- Temperature (T_L) (Liquidus)	217°C
	- Time (t_L)	60 -150 secs
Peak Temperature (T_P)		260 ^{+0/-5} °C
Time within 5°C of actual peak Temperature (t_p)		20 - 40 secs
Ramp-down Rate		6°C/second max
Time 25°C to peak Temperature (t)		8 minutes Max.
Do not exceed		260°C



1.0SMBJ / 1.0HSMBJ Series


Transient
Voltage Suppressor

Outline Drawing - SMB




SYMBOL	MILLIMETER		Inches	
	MIN	MAX	MIN	MAX
D	3.3	3.9	0.130	0.154
D1	1.7	2.3	0.067	0.091
T	5.1	5.7	0.201	0.224
T1	0.8	1.6	0.031	0.063
d	—	0.3	—	0.012
H1	2.0	2.4	0.079	0.094
H	2.1	2.5	0.083	0.098
L	4.0	4.7	0.157	0.185

Packaging Tape - SMB



SYMBOL	MILLIMETER
A0	3.60±0.1
B0	5.45±0.1
d0	1.50±0.1
d1	1.50±0.1
E	1.75±0.1
F	5.50±0.1
K0	2.30±0.1
P	8.00±0.1
P0	4.00±0.1
P1	2.00±0.1
W	12.00±0.1
T	0.22±0.02

Packaging Reel



SYMBOL	MILLIMETER
A	323±2
B	3.0±0.2
C	15.0±0.5
D	13±2
E	73±2
T1	2.2±0.2
Quantity	3000PCS

**BORN SEMICONDUCTOR, INC. ALL
RIGHT RESERVED**

Specifications are subject to change without notice.

Please refer to <http://www.born-tw.com> for current information.

Revision: 2022-Jan-1-A

