

MPD1030W2

Power Splitters/Combiners




APPLICATIONS

1. Multi-frequency signal combined
2. Indoor antenna distribution system Balanced Amplifiers
3. Multi-frequency Small Cell & Pico

Features

1. Low Insertion Loss 0.75dB typ based on IPD technology
2. Based on IPD technology
3. High isolation
4. Frequency covers a wide range of applications



Description

The MPD1030W2 is a low cost, high performance two ways power splitters in an easy to use surface mount package. It is ideal for multi-frequency signal combined, indoor antenna distribution system and multi-frequency Small Cell & Pico. MPD1030W2 is Based on IPD technology which possess excellent electrical and mechanical stability. All components are 100% RF tested.


Characteristics 1)

Item	Min.	Type.@25°C	Max.	Unit
Frequency Range	1000		3000	MHz
isolation	15	20		dB
Insertion Loss		0.75	1.05	dB
Phase Unbalance	-5	2	+5	degrees
Amplitude	-1	0.35	+1	dB
VSWR (:1)		1.35	2.0	:1
Operating Temp.	-55		+105	°C
Power			2	W

1) All the above data are based on specified demo board and tested in 25° environment.

PORT CONFIGURATIONS

Figure 1.MPD1030W2



All Use For RF & Microwave

Shenzhen Megsine technology co., ltd www.megsine.com sales@megsine.com may contain us for future information
Ju 09, 2021

MPD1030W2

Power Splitters/Combiners



2) Suggest to add a TVS Diode in parallel between electrode and Capacitors external connected to electrode to prevent DC signal entry to guarantee parts normal work.

Figure 2. MPD1030W2 electrical schematic



Typical Performance 25°C: (600-2600 MHz)

Figure 3. MPD1030W2 Insertion Loss





Figure 4. MPD1030W2 Return Loss



All Use For RF & Microwave


Shenzhen Megsine technology co., ltd www.megsine.com sales@megsine.com may contain us for future information
Ju 09, 2021

MPD1030W2

Power Splitters/Combiners



Figure 5. MPD1030W2 Isolation



Freq (MHz)

All Use For RF & Microwave

Shenzhen Megsine technology co., ltd www.megsine.com sales@megsine.com may contain us for future information
Ju 09, 2021

MPD1030W2

Power Splitters/Combiners



Outline Drawing

Figure 6. MPD1030W2 Outline Drawing





Figure 7. MPD1030W2 Recommended PCB Layout



Outline Dimensions (mm)

A	B	C	D	E	F	G	H	J
3.00	3.00	0.89	0.20	1.45	1.45	0.23	---	0.41
K	L	M	N	P	Q	R		wt
0.51	3.23	3.23	1.24	0.25	0.51	1.24		0.02

All Use For RF & Microwave

Shenzhen Megsine technology co., ltd www.megsine.com sales@megsine.com may contain us for future information
Ju 09, 2021


MPD1030W2

Power Splitters/Combiners



REFLOW PROFILE

Figure 8. Thermal Reflow Profile



	Ramp Up	Pre-Heating	Peak	Soaking
Temperature(°C)	T1:160±5°C	T2:180±5°C	T4:260±5°C	T3:230±5°C
Time(sec)	t1:60±5sec	t2:100±15sec	t3:30±5sec	t4:60±10sec

MPD1030W2

Power Splitters/Combiners



Device	Package	Reel	Shipping
MPD1030W2	QFN3*3	7 "	3000/Tape & Reel

All Use For RF & Microwave

Shenzhen Megsine technology co., ltd www.megsine.com sales@megsine.com may contain us for future information
Ju 09, 2021

MPD1030W2

Power Splitters/Combiners



Revision	Description	Date
Rev0	Preliminary	2023/07/18

All Use For RF & Microwave

Shenzhen Megsine technology co., ltd www.megsine.com sales@megsine.com may contain us for future information
Ju 09, 2021