



Product Specification

XBLW ULN2003

High-Voltage, High-Current Darlington Transistor Arrays


WEB | www.xinboleic.com




Descriptions

ULN2003 is high-voltage, high-current Seven Darlington arrays each containing seven open collector Darlington pairs with common emitters. Each channel is rated at 500 mA and can withstand peak currents of 600 mA. Suppression diodes are included for inductive load driving. The circuit is designed with a continuous diode, which can be used to drive the relay, stepper motor and other inductive loads. Single channel Darlington tube collector can output 500mA current. Higher output current capability is achieved by connecting Darlington tubes in parallel. The circuit can be widely used in relay driver, lighting driver, display driver (LED), stepper motor driver and logic buffer. It is useful for driving a wide range of loads including relay DC motors, LED display filament lamps, high-power buffers, 5V TTL, CMOS and other industry-standard logical circuit.

This chip is available in DIP-16 or SOP-16 package.



DIP-16



SOP-16

Feature

- Output current 500 mA per driver
- Withstand High Voltage (50V/60V two version)
- Input Pins Compatible to TTL/CMOS Logic Signal
- a Wide Application in Relay Driver

Applications

- Relay Driver
- Lamps Driver
- Display Driver

Ordering Information

Product Model	Package Type	Marking	Packing	Packing Qty	Remarks
XBLW ULN2003ALN	DIP-16	ULN2003ALN	Tube	1000Pcs/Box	50V
XBLW ULN2003ALDTR	SOP-16	ULN2003AL	Tape	2500Pcs/Reel	50V
XBLW ULN2003AN	DIP-16	ULN2003AN	Tube	1000Pcs/Box	60V
XBLW ULN2003ADTR	SOP-16	ULN2003A	Tape	2500Pcs/Reel	60V

Circuit Diagram




Figure 1 . Circuit Diagram

Pins Configuration




Figure 2 . Pins Configuration

Pins Description

No.	Name	Type	Description
1	1B	I	Input 1
2	2B	I	Input 2
3	3B	I	Input 3
4	4B	I	Input 4
5	5B	I	Input 5
6	6B	I	Input 6
7	7B	I	Input 7
8	E	-	Ground
9	COM	-	Common Free Wheeling Diodes
10	7C	O	Output 7
11	6C	O	Output 6
12	5C	O	Output 5
13	4C	O	Output 4
14	3C	O	Output 3
15	2C	O	Output 2
16	1C	O	Output 1

Absolute Maximum Ratings (T_A=25°C)

Parameter		Symbol	Min.	Max.	Unit
Collector-Emitter Voltage (Pin 10~ 16)	60V	V _{CE}	-0.5	60	V
	50V		-0.5	50	
Com Voltage (Pin 9)	60V	V _{COM}		60	V
	50V			50	
Input Voltage (Pin 1~7)		V _I	-0.5	30	V
Collector Peak Current		I _{CP}		500	mA/ch
Output Clamp Current		I _{OK}		500	mA
Emitter Maximum Current		I _{ET}		-2.5	A
Junction-To-Ambient Thermal Resistance	SOP16	θ _{JA}		63	°C/W
	DIP16			50	
Operating Temperature Range		T _{amb}	-40	85	°C
Maximum Junction Temperature		T _J		150	°C
Welding Temperature				260	°C, 10s
Storage Temperature Range		T _{stg}	-60	+150	°C
Power Dissipation	SOP16	P _D		1.28	W
	DIP16			1.5	

Recommended Operating Conditions

(T_A=25°C, unless otherwise noted)

Parameter		Symbol	Conditions	Min.	Max.	Unit
Collector-Emitter Voltage	60V	V _{CE}		0	60	V
	50V			0	50	
Maximum Junction Temperature		T _J			125	°C
Input Voltage		V _{IN}		0	24	V
Input Voltage (Output On)		V _{IN(ON)}	I _{OUT} =400mA, h _{FE} =800	2.5	24	V
Input Voltage (Output Off)		V _{IN(OFF)}		0	0.7	V
Clamp Forward Current		I _F			350	mA
Power Dissipation		P _D	T _A =-85°C		0.325	W

Electrical Characteristics (T_A=25°C)

Parameter	Test Diagrams	Test Conditions	Min.	Typ.	Max.	Unit
V _{I(ON)}	On-State Input Voltage	Figure 11 V _{CE} =2V	I _C =200mA		2.4	V
			I _C =250mA		2.7	
			I _C =300mA		3	
V _{OH}	High-Level Output Voltage After Switching	Figure 17 V _S =50V I _O =300m	60V	VS-50		mV
			50V	VS-50		
V _{CE(SAT)}	Collector-Emitter Saturation Voltage	Figure 10	I _I =250μA, I _C = 100mA	0.9	1.1	V
			I _I =350μA, I _C =200mA	1.0	1.3	
			I _I =500μA, I _C =350mA	1.4	1.6	
I _{CEX}	Collector Cutoff Current	Figure 16	V _{CE} =50V, I _I =0		50	μA
V _F	Clamp Forward Voltage	Figure 15	I _F =350mA	1.7	2	V
I _{I(off)}	Off-State Input Current	Figure 13	V _{CE} =50V, I _C =500μA	50	65	uA
I _I	Input Current	Figure 14	V _I =3.85V	0.93	1.35	mA
h _{FE}	Dc Forward Current Gain	Figure 10	V _{CE} =2V, I _C =350mA	1000		
I _R	Clamp Reverse Current	Figure 12	V _R =50V		50	μA
C _I	Input Capacitance		V _I =0, f= 1MHz	15	25	pF
t _{PLH}	Propagation Delay Time, Low- To High-Level Output	Figure 17		0.25	1	μS
t _{PHL}	Propagation Delay Time, High- To Low-Level Output	Figure 17		0.25	1	μS

Electrical Characteristics (T_A=-40°C ~ 85°C)

Parameter	Test Diagrams	Test Conditions	Min.	Typ.	Max.	Unit
V _{I(ON)}	On-State Input Voltage	Figure 11 V _{CE} =2V	I _C =200mA		2.7	V
			I _C =250mA		2.9	
			I _C =300mA		3	
V _{OH}	High-Level Output Voltage After Switching	Figure 17 V _S =50V I _O =300m	60V	VS-50		mV
			50V	VS-50		
V _{CE(SAT)}	Collector-Emitter Saturation Voltage	Figure 10	I _I =250μA, I _C = 100mA	0.9	1.2	V
			I _I =350μA, I _C =200mA	1.0	1.4	
			I _I =500μA, I _C =350mA	1.4	1.7	
I _{CEX}	Collector Cutoff Current	Figure 16	V _{CE} =50V, I _I =0		98	μA
V _F	Clamp Forward Voltage	Figure 15	I _F =350mA	1.7	2.3	V
I _{I(off)}	Off-State Input Current	Figure 13	V _{CE} =50V, I _C =500μA	30	65	uA
I _I	Input Current	Figure 14	V _I =3.85V	0.93	1.35	mA
I _R	Clamp Reverse Current	Figure 12	V _R =50V		100	μA
C _I	Input Capacitance		V _I =0, f= 1MHz	15	25	pF
t _{PLH}	Propagation Delay Time, Low- To High-Level Output	Figure 17		1.0	10	μS
t _{PHL}	Propagation Delay Time, High- To Low-Level Output	Figure 17		1.0	10	μS

Characteristic Curves




Figure 3. Collector-Emitter Saturation Voltage vs Collector Current




Figure 4. Collector-Emitter Saturation Voltage vs Total Collector Current (Two Darlings in Parallel)




Figure 5. Collector Current vs Input Current




Figure 6. Package Maximum Collector Current vs Duty Cycle




Figure 7. Input Current vs. Input Voltage




Figure 8. Collector Current vs. Saturation Voltage




Figure 9. Collector current vs. input current

Test Parameter Diagram




Figure 10. h_{FE} , $V_{CE(sat)}$ Test Circuit




Figure 11. $V_{I(on)}$ Test Circuit




Figure 12. I_R Test Circuit




Figure 13. $I_{I(off)}$ Test Circuit




Figure 14. I_I Test Circuit




Figure 15. V_F Test Circuit




Figure 16. I_{CEx} Test Circuit





Figure 16. I_{CEx} Test Circuit



Note: The capacitance load in Figure 17. is the parasitic capacitance of the oscilloscope probe.

Figure 17. Propagation Delay-Time Waveforms

Typical applications




Figure 18. ULN2003 Application Diagram


Application Instructions

Considering that some applications use microcontroller with pull-out resistance, the output state of microcontroller is uncertain when it is powered on and the ULN2003 input stage will be affected by the pull-out resistance of microcontroller and the load will be opened. In order to avoid the misaction of load, it is recommended that customers with such application problems connect a 4K pull-down resistance to the ground at the input stage, as shown in the Figure 18.

Package Information


DIP-16

Size Symbol	Dimensions In Millimeters		Size Symbol	Dimensions In Inches	
	Min(mm)	Max(mm)		Min(in)	Max(in)
A	3.710	4.310	A	0.146	0.170
A1	0.510		A1	0.020	
A2	3.200	3.600	A2	0.126	0.142
B	0.380	0.570	B	0.015	0.022
B1	1.524(BSC)		B1	0.060(BSC)	
C	0.204	0.360	C	0.008	0.014
D	18.80	19.20	D	0.740	0.756
E	6.200	6.600	E	0.244	0.260
E1	7.320	7.920	E1	0.288	0.312
e	2.540(BSC)		e	0.100(BSC)	
L	3.000	3.600	L	0.118	0.142
E2	8.400	9.000	E2	0.331	0.354



· SOP-16

Symbol	Size	Dimensions In Millimeters			Symbol	Size	Dimensions In Inches		
		Min(mm)	Nom(mm)	Max(mm)			Min(in)	Nom(in)	Max(in)
A		1.500	1.600	1.700	A		0.059	0.063	0.067
A1		0.100	0.150	0.250	A1		0.004	0.006	0.010
A2		1.400	1.450	1.500	A2		0.055	0.057	0.059
A3		0.600	0.650	0.700	A3		0.024	0.026	0.028
b		0.300	0.400	0.500	b		0.012	0.016	0.020
c		0.150	0.200	0.250	c		0.006	0.008	0.010
D		9.800	9.900	10.00	D		0.386	0.390	0.394
E		5.800	6.000	6.200	E		0.228	0.236	0.244
E1		3.850	3.900	3.950	E1		0.152	0.154	0.156
e		1.27 (BSC)			e		0.050 (BSC)		
L		0.500	0.600	0.700	L		0.020	0.024	0.028
L1		1.05 (BSC)			L1		0.041 (BSC)		
θ		0°	4°	8°	θ		0°	4°	8°



Statement:

- XBLW reserves the right to modify the product manual without prior notice! Before placing an order, customers need to confirm whether the obtained information is the latest version and verify the completeness of the relevant information.
- Any semi-guide product is subject to failure or malfunction under specified conditions. It is the buyer's responsibility to comply with safety standards when using XBLW products for system design and whole machine manufacturing. And take the appropriate safety measures to avoid the potential in the risk of loss of personal injury or loss of property situation!
- XBLW products have not been licensed for life support, military, and aerospace applications, and therefore XBLW is not responsible for any consequences arising from the use of this product in these areas.
- If any or all XBLW products (including technical data, services) described or contained in this document are subject to any applicable local export control laws and regulations, they may not be exported without an export license from the relevant authorities in accordance with such laws.
- The specifications of any and all XBLW products described or contained in this document specify the performance, characteristics, and functionality of said products in their standalone state, but do not guarantee the performance, characteristics, and functionality of said products installed in Customer's products or equipment. In order to verify symptoms and conditions that cannot be evaluated in a standalone device, the Customer should ultimately evaluate and test the device installed in the Customer's product device.
- XBLW documentation is only allowed to be copied without any alteration of the content and with the relevant authorization. XBLW assumes no responsibility or liability for altered documents.
- XBLW is committed to becoming the preferred semiconductor brand for customers, and XBLW will strive to provide customers with better performance and better quality products.