


# Actuator

704.410.01



<https://eao.com/p/704.410.01>

Your product:

---



704.410.01  
Actuator

#### FRONT

<b>Front dimension:</b>	Ø 29 mm
<b>Front bezel colour:</b>	Grey
<b>Front bezel material:</b>	Plastic

#### MOUNTING

<b>Design:</b>	raised
----------------	--------

#### OPERATING-/INDICATION PART

<b>Lever shape:</b>	short
<b>Lever material:</b>	plastic
<b>Lever colour:</b>	Black

#### ELECTRICAL CHARACTERISTICS

<b>Standards:</b>	The switches comply with the "Standards for low-voltage switching devices" DIN EN 60947-1
-------------------	---

#### MECHANICAL CHARACTERISTIC

<b>Switching action:</b>	Rest - Maintained
<b>Weight:</b>	0.034 kg
<b>Mechanical lifetime:</b>	≤2.5 Mio. cycles of operation
<b>Switching positions:</b>	2 positions
<b>Switching angle:</b>	90° right

## AMBIENT CONDITION

**IP Protection:** IP65 front side

**Storage temperature:** - 40 °C ... + 85 °C


## OTHER

**Hints:** Max. 3 switching elements can be clipped on

**max. number of switching elements:** 3


**Short Description:** Actuator, Ø 29 mm, optional illuminative, Black, short, Grey, Plastic, Rest - Maintained

**Dimension drawings:**



A = Screw terminal

**Mounting cut-outs:**




A = Screw terminal

B = Push-in terminal (PIT)

C = Plug-in terminal 6.3 mm x 0.8 mm

D = Double plug-in terminal 6.3 mm x 0.8 mm

**Switching positions:**



**Wiring diagrams:**

