







SPECIFICATION特性

- 1.Rating : DC 30V 0.5A;
- 1.额定值: 直流30V 0.5A
- 2.Contact resistance: $\leq 0.03\Omega$;
- 2.接触电阻: $\leq 0.03\Omega$;
- 3.Insulation resistance: $\geq 100M\Omega$ (DC250V);
- 3.绝缘电阻: $\geq 100M\Omega$ (DC250V)
- 4.Withstanvoltage: 500VAC ;
- 4.耐压: 500VAC
- 5.Insertion and extraction force: 3-20N;
- 5.插拔力: 3-20N;
- 6.life test: 5,000 cycles。
- 6.寿命试验: 5000次循环

SCHEMATIC



4	CONTACT FOOT	1	BRASS	Ag-Plating
3	SPRING	1	BR0NZE	Ag-Plating
2	CURVE PIECE	1	BRASS	Ag-Plating
1	HOUSING	1	PBT/PA66	
NO.	DESCRIPTION	QTY	MATERIAL	PLATING

广东星坤科技股份有限公司

DATE	REVISIONS
DATE	REVISIONS
DATE	REVISIONS
DATE	REVISIONS

文件工程章

DATE	REVISIONS	UNSPECIFIED TOLERANCES
DATE	REVISIONS	UNSPECIFIED TOLERANCES
DATE	REVISIONS	UNSPECIFIED TOLERANCES
DATE	REVISIONS	UNSPECIFIED TOLERANCES

DSND	SCALE: N/A	MODEL TYPE: DC POWER JACK
DWN	VIEW: 3/4	PART NO.: DC-038
CHKD	UNIT: mm/in	DWG NO.:
APPD	SIZE: A4	
WEIGHT	SHEET	REVISIC
	1/1	A0