








| 标 记<br>MARK | ECN编号/变更内容<br>ECN NO/DEFINITION | 修 改<br>REVISE | 日 期<br>DATE | 核 准<br>APPROVE |
|-------------|---------------------------------|---------------|-------------|----------------|
|             |                                 |               |             |                |
|             |                                 |               |             |                |


| CKI | DIM A | DIM B | DIM C | DIM D | DIM E |
|-----|-------|-------|-------|-------|-------|
| 2   | 3.96  | 8.68  | 10.61 | 11.88 | 3.88  |
| 3   | 7.92  | 12.64 | 14.57 | 15.84 | 7.84  |
| 4   | 11.88 | 16.60 | 18.53 | 19.80 | 10.00 |
| 5   | 15.84 | 20.56 | 22.49 | 23.76 | 10.00 |
| 6   | 19.80 | 24.52 | 26.45 | 27.72 | 10.00 |
| 7   | 23.76 | 28.48 | 30.41 | 31.68 | 10.00 |
| 8   | 27.72 | 32.44 | 34.37 | 35.64 | 10.00 |
| 9   | 31.68 | 36.40 | 38.33 | 39.60 | 10.00 |
| 10  | 35.64 | 40.36 | 42.29 | 43.56 | 10.00 |
| 11  | 39.60 | 44.32 | 46.25 | 47.52 | 10.00 |
| 12  | 43.56 | 48.28 | 50.21 | 51.48 | 10.00 |
| 13  | 47.52 | 52.24 | 54.17 | 55.44 | 10.00 |
| 14  | 51.48 | 56.20 | 58.13 | 59.40 | 10.00 |
| 15  | 55.44 | 60.16 | 62.09 | 63.36 | 10.00 |
| 16  | 59.40 | 64.12 | 66.05 | 67.32 | 10.00 |




Assembly Layout



2P



3P



技术指标:

- 1. 温度范围: -25℃~+85℃
- 2. 额定电压: 250V, AC/DC
- 3. 额定电流: 7.0A AC,DC
- 4. 接触电阻: ≤30mΩ Min
- 5. 耐 压: 1500V AC/minute
- 6. 绝缘电阻: ≥1000MΩ

|     |     |     |       |     |
|-----|-----|-----|-------|-----|
| 2   | 插针  | 铜   | 镀锡    |     |
| 1   | 基座  | LCP | 本色    |     |
| 序 号 | 品 名 | 材 质 | 电镀/颜色 | 备 注 |



深圳市虹成电子有限公司

|                |             |
|----------------|-------------|
| 品 名<br>TITLE   | 针座          |
| 料 号<br>PART NO | HCZZ0590-11 |

|                                          |                |        |                |      |
|------------------------------------------|----------------|--------|----------------|------|
| GENERAL TOLERANCES<br>(UNLESS SPECIFIED) | 比 列<br>SCALE   | 1:1    |                |      |
| X. ±0.50 .XX ±0.10                       | 单 位<br>UNIT    | MM     | 制 图<br>DRAW    | AhYe |
| .X ±0.20 .XXX ±0.05                      | 张 数<br>PART NO | 1 OF 1 | 审 核<br>CHECKED | 夏操云  |
| ANGLES ±1°                               | 版 本<br>REV     | A      | 批 准<br>APPROVE | 赵亮亮  |

