






| 标 记<br>MARK | ECN编号/变更内容<br>ECN NO/DEFINITION | 修 改<br>REVISE | 日 期<br>DATE | 核 准<br>APPROVE |
|-------------|---------------------------------|---------------|-------------|----------------|
|             |                                 |               |             |                |
|             |                                 |               |             |                |

| CKI | DIM A | DIM B | DIM C |
|-----|-------|-------|-------|
| 2   | 2.00  | 6.0   | 3.2   |
| 3   | 4.00  | 8.0   | 3.2   |
| 4   | 6.00  | 10.00 | 3.0   |
| 5   | 8.00  | 12.00 | 5.0   |
| 6   | 10.00 | 14.00 | 7.0   |
| 7   | 12.00 | 16.00 | 9.0   |
| 8   | 14.00 | 18.00 | 11.0  |
| 9   | 16.00 | 20.00 | 13.0  |
| 10  | 18.00 | 22.00 | 15.0  |
| 11  | 20.00 | 24.00 | 17.0  |
| 12  | 22.00 | 26.00 | 19.0  |
| 13  | 24.00 | 28.00 | 21.0  |
| 14  | 26.00 | 30.00 | 23.0  |
| 15  | 28.00 | 32.00 | 25.0  |
| 16  | 30.00 | 34.00 | 27.0  |



适用线路板(PCB LAYOUT)

技术指标:

- 1.工作温度: -25℃~85℃
- 2.额定电压: 250V, DC/AC(rms)
- 3.耐 压 值: 800V AC/minute
- 4.接触电阻: ≤20mΩ
- 5.绝缘电阻: ≥1000MΩ
- 6.额定电流: 3.0A AC,DC
- 7.适用线规: AWG#28~#22

| 2   | 插针  | 铜   | 镀锡    |     |
|-----|-----|-----|-------|-----|
| 1   | 基座  | LCP | 本色    |     |
| 序 号 | 品 名 | 材 质 | 电镀/颜色 | 备 注 |



深圳市虹成电子有限公司

| 品 名<br>TITLE   | 针座                |
|----------------|-------------------|
| 料 号<br>PART NO | HC-PHB2. 0-2x5PWT |

| GENERAL TOLERANCES<br>(UNLESS SPECIFIED) | 比 列<br>SCALE   | 1:1    | 制 图<br>DRAW    | AhYe |  |
|------------------------------------------|----------------|--------|----------------|------|--|
| X. ±0.50 .XX ±0.10                       | 单 位<br>UNIT    | MM     | 审 核<br>CHECKED | 夏操云  |  |
| .X ±0.20 .XXX ±0.05                      | 张 数<br>PART NO | 1 OF 1 | 批 准<br>APPROVE | 赵亮亮  |  |
| ANGLES ±1°                               | 版 本<br>REV     | A      |                |      |  |