


Description:

This N-Channel MOSFET uses advanced trench technology to minimize on-state resistance, provide superior switching performance, and withstand high energy pulse in the avalanche and commutation mode. These devices are well suited for high efficiency fast switching applications.

Features:

- 1) $V_{DS}=20V, I_D=75A, R_{DS(ON)} < 4m\Omega @ V_{GS}=4.5V$
- 2) Improved dv/dt capability
- 3) Fast switching
- 4) 100% EAS Guaranteed
- 5) Green Device Available.



Package Marking and Ordering Information:

Part NO.	Marking	Package	Packing
DOZ75N02	75N02	DFN3*3-8	5000 pcs/Reel

Absolute Maximum Ratings: ($T_c=25^\circ\text{C}$ unless otherwise noted)

Symbol	Parameter	Ratings	Units
V_{DS}	Drain-Source Voltage	20	V
V_{GS}	Gate-Source Voltage	± 12	V
I_D	Continuous Drain Current-Continuous- $T_c=25^\circ\text{C}$	75	A
	Continuous Drain Current-Continuous- $T_c=100^\circ\text{C}$	45	A
I_{DM}	Drain Current – Pulsed	240	A
EAS	Single Pulse Avalanche Energy	110	mJ
P_D	Power Dissipation - $T_c=25$	26	W
T_J, T_{STG}	Operating and Storage Junction Temperature Range	-55 to +150	$^\circ\text{C}$

Thermal Characteristics:

Symbol	Parameter	Max	Units
$R_{\theta JC}$	Thermal Resistance, Junction to Case	4.3	$^\circ\text{C}/\text{W}$

Electrical Characteristics: ($T_C=25^{\circ}\text{C}$ unless otherwise noted)

Symbol	Parameter	Conditions	Min	Typ	Max	Units
Off Characteristics						
BV _{DSS}	Drain-Sourctce Breakdown Voltage	V _{GS} =0V, I _D =250 μ A	20	---	---	V
I _{DSS}	Drain-Source Leakage Current	V _{GS} =0V, V _{DS} =20V	---	---	1	μ A
I _{GSS}	Gate-Source Leakage Current	V _{GS} = ± 12V, V _{DS} =0A	---	---	± 100	nA
On Characteristics						
V _{GS(th)}	GATE-Source Threshold Voltage	V _{GS} =V _{DS} , I _D =250 μ A	0.4	0.7	1.0	V
R _{DS(ON)}	Drain-Source On Resistance	V _{GS} =4.5V, I _D =30A	---	2.8	4	m Ω
		V _{GS} =2.5V, I _D =20A	---	4	6	
Dynamic Characteristics						
C _{iss}	Input Capacitance	V _{DS} =10V, V _{GS} =0V, f=1MHz	---	3199	---	pF
C _{OSS}	Output Capacitance		---	459	---	
C _{rss}	Reverse Transfer Capacitance		---	445	---	
Switching Characteristics						
t _{d(on)}	Turn-On Delay Time	V _{DD} =10V , V _{GS} =4.5V , R _G =1.8 Ω , I _D =30A	---	9.7	---	ns
t _r	Rise Time		---	36	---	ns
t _{d(off)}	Turn-Off Delay Time		---	62	---	ns
t _f	Fall Time		---	52	---	ns
Q _g	Total Gate Charge	V _{DS} =10V , V _{GS} =4.5V , I _D =30A	---	48	---	nC
Q _{gs}	Gate-Source Charge		---	3.5	---	nC
Q _{gd}	Gate-Drain “Miller” Charge		---	18	---	nC
Drain-Source Diode Characteristics						
I _S	Continuous Source Current	VD=VG=0V	---	---	75	A
I _{SM}	Pulsed Source Current		---	---	360	A

V_{SD}	Forward on voltage	$I_S=30A, V_{GS}=0V$	---	---	1.2	V
T_{rr}	Body Diode Reverse Recovery Time	$I_F=30A, dI/dt=100A/\mu s$	---	23	---	nS
Q_{rr}	Body Diode Reverse Recovery Charge		---	10	---	nC

Notes:

1. Repetitive Rating: Pulse Width Limited by Maximum Junction Temperature
2. EAS condition : $T_J=25^\circ C$, $V_{DD}=15V$, $V_G=4.5V$, $L=0.5mH$, $R_g=25\Omega$, $I_{AS}=21A$
3. Pulse Test: Pulse Width $\leq 300\mu s$, Duty Cycle $\leq 0.5\%$

Typical Characteristics: ($T_C=25^\circ C$ unless otherwise noted)




Figure1: Output Characteristics




Figure 2: Typical Transfer Characteristics




Figure 3: On-resistance vs. Drain Current




Figure 4: Body Diode Characteristics




Figure 5: Gate Charge Characteristics




Figure 6: Capacitance Characteristics




Figure 7: Normalized Breakdown Voltage vs. Junction Temperature




Figure 8: Normalized on Resistance vs. Junction Temperature




Figure 9: Maximum Safe Operating Area




Figure 10: Maximum Continuous Drain Current vs. Case Temperature






Figure.11: Maximum Effective Transient Thermal Impedance, Junction-to-Case

DFN3X3-8 Package Information:



SYMBOL	DIMENSIONAL REQMTS		
	MIN	NOM	MAX
A	0.70	0.75	0.80
b	0.25	0.30	0.35
c	0.10	0.15	0.25
D	3.25	3.35	3.45
D1	3.00	3.10	3.20
D2	1.78	1.88	1.98
D3	---	0.13	---
E	3.20	3.30	3.40
E1	3.00	3.15	3.20
E2	2.39	2.49	2.59
e	0.65BSC		
H	0.30	0.39	0.50
L	0.30	0.40	0.50
L1	---	0.13	---
θ	---	10°	12°
M	*	*	0.15

* Not specified



UNIT: mm

Marking Information:


①. Part NO.

②. Date Code(YWWG / R)

Y : Year Code , last digit of the year

WW : Week Code(01-53)

G/R : G(Green) /R(Lead Free)



Attention :

- Information furnished in this document is believed to be accurate and reliable. However, Shenzhen Doingter Semiconductor Co.,Ltd. assumes no responsibility for the consequences of use without consideration for such information nor use beyond it.
 - Information mentioned in this document is subject to change without notice, apart from that when an agreement is signed, Shenzhen Doingter complies with the agreement. Products and information provided in this document have no infringement of patents.
 - Shenzhen Doingter assumes no responsibility for any infringement of other rights of third parties which may result from the use of such products and information. This document supersedes and replaces all information previously supplied.
-  Is a registered trademark of Shenzhen Doingter Semiconductor Co., Ltd. Copyright © 2013 Shenzhen Doingter Semiconductor Co.,Ltd. Printed All rights reserved.