









SIM CARD	
Pin No.	NAME
C1	VCC
C2	RST
C3	CLK
C5	GND
C6	VPP
C7	I/O

NOTES:

1) MATERIAL:

- 1-1 HOUSING: THERMOPLASTIC, UL 94V-0; COLOR: BLACK
- 1-2 SHIELDED: STAINLESS STEEL SUS304-3/4H
- 1-3 CONTACT: COPPER ALLOY C5191-EH

2) FINISH:

- 2-1 CONTACT: Au PLATING ON CONTACT AREA
(SEE P/N DESCRIPTION)
50u" MIN NICKEL UNDERPLATING OVER ALL
100u" MIN MATTE TIN PLATING ON SOLDER AREA
- 2-2 SHIELDED: 1u" MIN Au PLATING ON SECURED AREA

3) PRODUCT SPECIFICATIONS:


- 3-1 VOLTAGE RATING: 50V
- 3-2 WITHSTANDING VOLTAGE: AC250V R.M.S
- 3-3 CURRENT RATING: 0.5A
- 3-4 INSULATION RESISTANCE: 1000MEG.OHM MIN AT DC 250V
- 3-5 CONTACT RESISTANCE: 100 MILL.OHM MAX
- 3-6 OPERATION TEMPERATURE: -20° TO +85°
- 3-7 DURABILITY: 3000 CYCLES



深圳市华宇创精密电子有限公司

TOLERANCE:

X.X ± 0.30
X.XX ± 0.25
X.XXX ± 0.15
X.' $\pm 2'$ X.X' $\pm 0.5'$



UNIT: mm [inch]

SCALE: 1:1 SIZE: A4

DRAWN BY :

陈一鸣

DATE :

2014-02-23

PART NAME:

NANO SIM 6P 掀盖 (带检测PIN)

CHECKED BY:

马跃

DATE :

2014-02-23

PART NO.

HYCW241-SIM06-140B

APPROVED BY:

柯南

DATE :

2014-02-23

DRAW NO:

HYC-SIM191128141

SHEET NO.

1 OF 1