

标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE

CKI	DIM A	DIM B
2	2.00	6.0
3	4.00	8.0
4	6.00	10.00
5	8.00	12.00
6	10.00	14.00
7	12.00	16.00
8	14.00	18.00
9	16.00	20.00
10	18.00	22.00

A

B

C

D

E

F

G

A

B





C

D

E

F



G



2P 结构样式

技术指标:

1. 工作温度: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$
2. 额定电压: 250V, DC/AC(rms)
3. 额定电流: 3.0A AC,DC
4. 接触电阻: $\leq 20\text{m}\Omega$
5. 耐 压: 800V AC/minute
6. 绝缘电阻: $\geq 1000\text{M}\Omega$
7. 适用线规: AWG#28~#22



2	插针	铜	镀锡	
1	基座	LCP	本色	
序 号	品 名	材 质	电镀/颜色	备 注



深圳市虹成电子有限公司

品 名 TITLE	针座
料 号 PART NO	HC-PHD2. 0-2x6PLT

GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1			
X. ± 0.50	.XX ± 0.10	单 位 UNIT	MM	制 图 DRAW	AhYe	
.X ± 0.20	.XXX ± 0.05	张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云	
ANGLES $\pm 1^{\circ}$		版 本 REV	A	批 准 APPROVE	赵亮亮	