

标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE

A

B


C

D

E








F

G



SECTION A-A

3D VIEW



PAD AREA (TOP VIEW)

NOTES:

- MATERIAL:
 - HOUSING: LCP ,COLOR IS BLACK;
 - CONTACT: PHOSPHOR COPPER (C5191 T=0.30mm);
- FINISH: GOLD PLATED G/Fu”;
- ELECTRICAL:
 - VOLTAGE RATING: 125 VAC RMS;
 - CURRENT RATING: 1.5 AMP;
 - CONTACT RESISTANCE: 35MILLIOHMS MAX.;
 - WITHSTAND VOLTAGE: 500 VAC RMS 50(60)Hz,1MIN.;
 - INSULATION RESISTANCE: 500MEGOHMS MIN @500V DC.;
- MECHANICAL:
 - MATING/UNMATING FORCE: 22N MAX.;
 - RETENTIION STRENGTH: 50N MIN.;
 - OPERATING LIFE: 750 CYCLES MIN.;
- ENVIRONMENTAL:
 - STORAGE TEMPERATURE RANGE: -40℃~+85℃;
 - OPERATION TEMPERATURE RANGE: -25℃~+70℃;
- SALT SPRAY TEST:8H(EXCLUDING RIVETED BENDS)

2	接触	铜	镀金G/F	
1	基座	LCP	黑色	
序 号	品 名	材 质	电镀/颜色	备 注

	深圳市虹成电子有限公司		品 名 TITLE	网口	
			料 号 PART NO	HC-WK88-H865T-QS	
UNLESS OTHERWISE, GENERAL TOLERANCE:		比 列 SCALE	1:1		
X. xxx ±0.10 X. xx ±0.20 X. x ±0.30		单 位 UNIT	MM	制 图 DRAW	AhYe
ANGULAR: X. xx° ±1° X. x° ±3° X. ° ±5°		张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云
		版 本 REV	A	批 准 APPROVE	赵亮亮

