








标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE


CKI	DIM A	DIM B	DIM C	DIM D	DIM E
2	3.96	8.68	10.61	11.88	3.88
3	7.92	12.64	14.57	15.84	7.84
4	11.88	16.60	18.53	19.80	10.00
5	15.84	20.56	22.49	23.76	10.00
6	19.80	24.52	26.45	27.72	10.00
7	23.76	28.48	30.41	31.68	10.00
8	27.72	32.44	34.37	35.64	10.00
9	31.68	36.40	38.33	39.60	10.00
10	35.64	40.36	42.29	43.56	10.00
11	39.60	44.32	46.25	47.52	10.00
12	43.56	48.28	50.21	51.48	10.00
13	47.52	52.24	54.17	55.44	10.00
14	51.48	56.20	58.13	59.40	10.00
15	55.44	60.16	62.09	63.36	10.00
16	59.40	64.12	66.05	67.32	10.00




Assembly Layout



2P



3P



技术指标:

- 1. 温度范围: -25℃~+85℃
- 2. 额定电压: 250V, AC/DC
- 3. 额定电流: 7.0A AC,DC
- 4. 接触电阻: ≤30mΩ Min
- 5. 耐 压: 1500V AC/minute
- 6. 绝缘电阻: ≥1000MΩ

2	插针	铜	镀锡	
1	基座	LCP	本色	
序 号	品 名	材 质	电镀/颜色	备 注



深圳市虹成电子有限公司

品 名 TITLE	针座
料 号 PART NO	HCZZ0590-9

GENERAL TOLERANCES (UNLESS SPECIFIED)	比 列 SCALE	1:1	制 图 DRAW		AhYe	审 核 CHECKED	夏操云	批 准 APPROVE	赵亮亮
X. ±0.50 .XX ±0.10	单 位 UNIT	MM							
.X ±0.20 .XXX ±0.05	张 数 PART NO	1 OF 1							
ANGLES ±1°	版 本 REV	A							

