







标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE



SPECIFICATION (技术要求)

1. Operating Temperature(环境温度): -25℃~85℃
2. Voltage Rating(额定电压): 50V AC/DC
3. Current Rating(额定电流): 0.5A
4. Contact Resistance(接触抗阻): 30mΩ
5. Insulation Resistance(绝缘抗阻): 100MΩ
6. Dielectric Withstanding Voltage(耐电压): 500V AC Min
7. Insertion/Withdrawal Force(插拔力): 3-50N
8. Life Time(mating cycles)寿命: >1000 Cycles
9. SIGNAL LOSS<1dB IN BOTH VHF, UHF BAND.
10. NOMINAL IMPEDANCE : 75 OHMS.
11. OPERATING FREQUENCY : 0-2 GHZ.



铆接处焊锡

3	IEC母头	冷扎板	镀镍	
2	支架	SPCC	镀铜锡	
1	绝缘体	PPS	棕色	
序 号	品 名	材 质	电镀/颜色	备 注




深圳市虹成电子有限公司

品 名 TITLE	屏蔽罩
料 号 PART NO	HC-PBZ-I041

GENERAL TOLERANCES
(UNLESS SPECIFIED)

比 列
SCALE

1:1



.XX±0.20 X±0.40

单 位
UNIT

MM

制 图
DRAW

AhYe

.X±0.30 ANGULAR: ±2°

张 数
PART NO

1 OF 1

审 核
CHECKED

夏操云

版 本
REV

A

批 准
APPROVE

赵亮亮

