








3D VIEW



RECOMMENDED PCB LAYOUT THICKNESS=1.6mm
TOP VIEW;TOLERANCE=±0.05

NOTES:

1.MATERIAL:SEE TABLE

2.PLATING:SEE TABLE

3.ELECTRICAL PERFORMANCE:

CONTACT RESISTANCE:INITIAL CONTACT RESISTANCE

EXCLUDING CONDUCTOR RESISTANCE:10 MILLIOHMS MAX

DIELECTRIC STRENGTH:UNMATED CONNECTORS APPLY 500V AC

MATED CONNECTOR APPLY 300V AC

INSULATION RESISTANCE:100 MEGAOHMS MIN.(UNMATED)

10 MEGAOHMS MIN.(MATED)

4.ALL MATERIALS NEED TO MEET ROHS2 + HF

ENVIRONMENTAL AND SAFETY REQUIREMENTS

TABLE:

NO	PART	Q'TY	Material
1	SHELL	1	STAINLESS STEEL T=0.4mm,Ni PLATED 50u"Min
2	TERMINAL	19	COPPER ALLOY T=0.2mm,NI 50u"Min;Au G/F;Au u"
3	HOUSING	1	LCP UL 94V-0 BLACK
4	COVER	1	LCP UL 94V-0 BLACK



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: HDMI A TYPE 立式贴片15.0H	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW112-HDMI A19-150B	MOLD NO.
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱国夷	DATE : 2014-02-23	DRAW NO: HYC-1911301025	
			SHEET NO. 1 OF 1	