






NOTE :

1. SPECIFICATION:

- 1.1. CURRENT RATING: 0.5 Amp Max.
- 1.2. VOLTAGE RATING: 40 V ac(r.m.s) Max.
- 1.3. CONTACT RESISTANCE: 10m ohms Max.mated
- 1.4. INSULATION RESISTANCE:100M ohms Min.
- 1.5. DIELECTRIC WITHSTANDING VOLTAGE:
AC 500V Min. (for 1 minute)

- 1.6. OPERATION TEMPERATURE RANGE:-25° C~85° C


2. MECHANICAL

- 2.1. INSERTION FORCE:4.5KGF MAXMUM
- 2.1. WITHDRAWAL FORCE:1.0KGF MINIMUM;4.0KGF MAXMUM
- 2.3. DURABILITY:10000 CYCLES AT 100±50 CYCLES PERHOUR, CONTACT CHANCE FROM INITIAL VALUE:30MINI Ohms MAX

”▲ ”为品管重点管控尺寸



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2' X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: HDMI A TYPE 公座夹板1.2	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW125-HDMI19-120B	MOLD NO.
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-HDMI201217301	SHEET NO. 1 OF 1