## HF7FD

### SUBMINIATURE HIGH POWER RELAY



File No.:E134517



File No.: R50457893



File No.: 40008374



File No.:CQC16002153649



#### **Features**

- 20A switching capability
- TV-12 load capability
- 2kV dielectric strength (between coil and contacts)
- The ambient temperature can reach 105°C
- Product in accordance to IEC 60335-1 available
- Double pins type available
- 1 Form A and 1 Form C configurations
- UL insulation system:Class F

CONTACT DATA				
Contact arrangement	1A 10		1C	
Contact resistance <sup>1)</sup>	100mΩ max.(1A 24VDC			
Contact material			AgSnO <sub>2</sub>	
Contact rating (Res.load)	16A 250VAC 20A 250VAC		NO: 16A 250VAC 20A 250VAC NC: 7A 250VAC/28VDC 10A 250VAC	
Max. switching voltage	277VAC / 28VI		277VAC / 28VDC	
Max. switching current	20A		20A	
Max. switching power	5000VA / 280W		5000VA /280W	
Mechanical endurance			1 x 10 <sup>7</sup> OPS	
Electrical endurance (See approval reports for more details)	HF7FD	NO:85°C 16A 250VAC 5 x 10°OPS Resistive load, 1s on 9s o NO:85°C 20A 250VAC 5 x 10°OPS Resistive load, 1s on 9s o NC:85°C 10A 250VAC 5 x 10°OPS Resistive load, 1s on 9s o		
	HF7FD-T	NO:105°C 17A 125VAC 1x 10°OP Resistive load, 1s on 9s on NO:105°C 12A 250VAC 1x 10°OP Resistive load, 1s on 9s on NO:105°C 12A 250VAC 1x 10°OP		

Notes: 1) The data shown above are initial values.
2) Open the air permeability hole when testing plastic encapsulated products.

#### **CHARACTERISTICS** 100MΩ (at 500VDC) Insulation resistance 2000VAC 1min Between coil & contacts Dielectric strength Between open contacts 750VAC 1min Operate time (at nomi. volt.) 10ms max. Release time (at nomi. volt.) 5ms max. 5% to 85% RH Humidity Functional 98m/s<sup>2</sup> Shock resistance Destructive 980m/s<sup>2</sup> Ambient temperature -40°C to 105°C Vibration resistance 10Hz to 55Hz 1.5mm DA Termination **PCB** Approx. 10g Unit weight Plastic sealed, Construction Flux proofed

Notes: 1) The data shown above are initial values. 2) If the ambient temperature is higher than 85°C, please contact Hongfa.

COIL	
Coil power	Approx. 360mW

COIL DATA at 23°C				
Nominal Voltage VDC	Pick-up Voltage VDC max. <sup>1)</sup>	Drop-out Voltage VDC min. <sup>1)</sup>	Max. Voltage VDC <sup>2)</sup>	Coil Resistance Ω
3	2.25	0.3	3.9	25 x (1±10%)
5	3.75	0.5	6.5	70 x (1±10%)
6	4.50	0.6	7.8	100 x (1±10%)
9	6.75	0.9	11.7	225 x (1±10%)
12	9.00	1.2	15.6	400 x (1±10%)
18	13.5	1.8	23.4	900 x (1±10%)
24	18.0	2.4	31.2	1600 x (1±15%)
48	36.0	4.8	62.4	6400 x (1±15%)

Notes: 1) The data shown above are initial values.

2)\*Maximum voltage refers to the maximum voltage which relay coil could endure in a short period of time.

SAFET	ΥΑ	PPR	OVAL	RAT	INGS
					NO:20A


UL/CUL	HF7FD	NO:20A 250VAC 85°C (530)  16A 250VAC Resistive load / General load 85°C  TV-10 240VAC/120VAC 40°C (530)  TV-8 120VAC 40°C (590)  1HP 250VAC 40°C  1/2HP 125VAC 40°C  NC:10A 250VAC 85°C (530)  10A 250VAC 40°C  7A 277VAC 85°C  7A 28VDC 85°C	
	HF7FD-T	NO:17A 125VAC 105°C TV-10 240VAC/120VAC 40°C (530) TV-8 120VAC 40°C (590) 16A 250VAC Resistive load / General load 85°C 1HP 250VAC 40°C 1/2HP 125VAC 40°C NC:12A 277VAC/250VAC/120VAC 105°C 10A 250VAC 40°C	
VD5	HF7FD	NO:16A 250VAC 85°C 17A 250VAC 85°C (530) NO:10A 250VAC 85°C 7A 250VAC 85°C	
VDE	HF7FD-T	NO:16A 250VAC 105°C 12A 250VAC 105°C NC:7A 250VAC 105°C	
TUV	HF7FD	NO:16A 250VAC 85°C 17A 250VAC 85°C (530) 20A 250VAC 85°C (530) NC:10A 250VAC 85°C (530)	
HF7FD		NO:20A 250VAC 85°C NO:16A 250VAC 85°C NC:10A 250VAC 85°C	
CQC	HF7FD-T	NO:16A 250VAC 105°C NC:10A 250VAC 105°C	

Notes:Only typical loads are listed above. Other load specifications can be available upon request.



HONGFA RELAY

ISO9001, IATF16949, ISO14001, ISO45001, IECQ QC 080000, ISO/IEC 27001 CERTIFIED




Notes: 1) Under the ambience with dangerous gas like H<sub>2</sub>S, SO<sub>2</sub> or NO<sub>2</sub>, plastic sealed type is recommended; Please test the relay in real applications. If the ambience allows, flux proofed type is preferentially recommended.

- 2) Contact is recommended for suitable condition and specifications if water cleaning or surface process is involved in assembling relays on PCB
- 3) If plastic sealed type is selected for cleaning purpose, the vent-hole cover should be excised after cleaning.

#### OUTLINE DIMENSIONS, WIRING DIAGRAM AND PC BOARD LAYOUT

Unit: mm




# **PCB** Layout **Outline Dimensions** Wiring Diagram (Bottom View) (Bottom view) (530)1 Form A 0.36x2 (530)1 Form C 22 4xR0.5 2x0.4 0.36x2 1 Form A (Double pins type) 22 5xØ1.4 1 Form C (Double pins type) 12.2 2.8 6xØ1.4 1x0.4


Remark:1) The pin dimension of the product outline drawing is the size before tinning (it will become larger after tinning), and the mounting hole size is the recommended design size of the PCB board hole. The specific PCB board hole design size can be mapped and adjusted according to the actual product.
2) In case of no tolerance shown in outline dimension: outline dimension ≤1mm, tolerance should be ±0.2mm; outline dimension >1mm and ≤5mm, tolerance should be ±0.3mm; outline dimension >5mm, tolerance should be ±0.4mm.
3) The tolerance without indicating for PCB layout is always ±0.1mm.

#### **CHARACTERISTIC CURVES**


#### MAXIMUM SWITCHING POWER



#### **ENDURANCE CURVE**



#### COIL TEMPERATURE RISE



#### Percent of Nominal Voltage (%)

#### Test conditions:

Curve A: NO, Resistive load, 85°C, flux proofed, 16A 250VAC, 1s on 9s off Curve B: NO, Resistive load, 85°C, flux proofed, 20A 250VAC, 1s on 9s off

#### Test conditions::

A:20A at 85°C. B:16A at 85°C.

Mounting distance: 25mm

#### Disclaimer

The specification is for reference only. See to "Terminology and Guidelines" for more information. Specifications subject to change without notice. We could not evaluate all the performance and all the parameters for every possible application. Thus the user should be in a right position to choose the suitable product for their own application. If there is any query, please contact Hongfa for the technical service. However, it is the user's responsibility to determine which product should be used only.

© Xiamen Hongfa Electroacoustic Co., Ltd. All rights of Hongfa are reserved.