







PCB LAYORT (TOP VIEW)

TOLERANCE: ±0.05



STEP 1 INSERT NANO SIM CARD



STEP 2 PUSH THE SHELL

SIM CARD PIN ON	NAME
PIN_1	VCC
PIN_2	RST
PIN_3	CLK
PIN_5	GND
PIN_6	VPP
PIN_7	I/O

NOTES:

1. MATERIAL:

1-1 HOUSING: THERMOPLASTIC, UL94 V-0 . COLOR:BLACK

1-2 SHELL; STAINLESS STEEL T=0.20mm

1-3 CONTACT: COPPER ALLOY T=0.15mm

2. FINISH:

2-1 CONTACT: 1u" AU MIN. ON CONTACT AREA

GOLD FLASH ON SOLD AREA.

50u" NI MIN. UNDERPLATING OVER ALL



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2" X.X' ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: NANO SIM 6P 掀盖 1.5H
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW359-SIM06-150B
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.
			DRAW NO: HYC-2405141256
			SHEET NO. 1 OF 1