

STRADA Whisper 3.9mm


TE Internal #: 2187658-1

48 Position High Speed Backplane Connector, 4 Row, 6 Column,
PCB Mount Receptacle, Right Angle, Unshrouded, STRADA
Whisper 3.9mm

[View on TE.com >](#)



Connectors > PCB Connectors > Backplane Connectors > High Speed Backplane Connectors



Number of Positions: 48
Row-to-Row Spacing: 2.5 mm [.098 in]
Mating Alignment: With
Mating Alignment Type: Keyed
Number of Rows: 4

Features

Electrical Characteristics

Operating Voltage	80 VAC
Impedance	100 Ω

Signal Characteristics

Data Rate	56 Gb/s
Differential Impedance	100 Ω
Number of Differential Pairs per Column	8

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
---------------------------	--------------------------

Industry Standards

Compatible With Agency/Standards Products	UL
UL Flammability Rating	UL 94V-0
Compatible With Approved Standards Products	UL E28476

Body Features

--	--



Shield Material	Copper Alloy
Primary Product Color	Black

Packaging Features

Packaging Method	Tube
------------------	------

Operation/Application

Durability Rating	200 Cycles
Circuit Application	Signal

Contact Features

Contact Shape & Form	Dual Beam
Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Tin
Contact Type	Receptacle
Contact Current Rating (Max)	.4 A

Housing Features

Number of Shrouded Sides	0
Housing Material	LCP (Liquid Crystal Polymer)
Centerline (Pitch)	3.9 mm[.154 in]

Product Type Features

Signal Arrangement	Differential
Connector & Contact Terminates To	Printed Circuit Board
Connector System	Board-to-Board
Backplane Module Type	Center
PCB Connector Assembly Type	PCB Mount Receptacle
Shroud Style	Unshrouded

Mechanical Attachment

Guide Hardware	Without
PCB Mount Retention	With
Mating Retention	Without
PCB Mount Retention Type	Action/Compliant Tail
Mating Alignment	With
Mating Alignment Type	Keyed

Configuration Features

--	--



Number of Pairs	24
Number of Ground Positions	30
Number of Signal Positions	48
Number of Power Positions	48
Backplane Architecture	Traditional Backplane
Pairs per Column	4
Number of Positions	48
Number of Rows	4
Number of Columns	6
PCB Mount Orientation	Right Angle

Dimensions

Row-to-Row Spacing	2.5 mm[.098 in]
--------------------	-----------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as



EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 2187510-1
SW PIR HDR BP, 100OHM, 4X6 OEW

Also in the Series

STRADA Whisper 3.9mm



High Speed Backplane Cable
Assemblies(16)



High Speed Backplane Connectors(41)

Customers Also Bought



TE Part #1-2324271-3
RIGHT SEGMENT LGA4189-4
SOCKETP4 FOR ODM



TE Part #1-2324271-4
LEFT SEGMENT LGA4189-4 SOCKET-
P4 FOR ODM



TE Part #1-2340321-2
ASSY STRADDLE MOUNT 168P 076
SLIVER 2.0



TE Part #2327677-3
RECEPT ASSY, 140 POS, VERT, SLIVER
2.0





TE Part #2327678-3
RECEPTACLE ASSY, 84 P, VERT,
SLIVER 2.0

TE Part #2344604-2
50 AMP CARD EDGE ASSEMBLY

TE Part #2474708-2
RCPT CONN 76 POSN QSFP-DD 112

TE Part #1-2204456-3
MULTI-BEAM HD R/A PLUG 2P+15S

TE Part #2-2332141-0
RECEPTACLE ASSY, 56POS, VERT,
SLIVER 2.0

TE Part #2356580-2
SOCKET P4 TFLM KIT W/ COVER

Documents

Product Drawings

SW PIR RECT, 100OHM, 4X6

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2187658-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2187658-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2187658-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

STRADA Whisper 3.9mm 100-Ohm Pair-In-Row Right-Angle Receptacle Connector Routing Guide

English